

## ECM-LZ1UBMP

DWZ Series digital wireless uni-directional electret condenser lavalier microphone



### Overview

#### **High quality lavalier microphone ideal for presenters and vocalists**

The ECM-LZ1UBMP works with the ZTX-B02RC body-pack transmitter and is supplied with the DWZ-B70HL package. The uni-directional electret condenser lavalier microphone is ideal for commercial sound applications such as presentations, lectures and conferences. Comes supplied with mic holder clip and windscreen.

### Specifications

#### Audio Section

|                           |                                       |
|---------------------------|---------------------------------------|
| Capsule Type              | Electret Condenser                    |
| Frequency Response        | 60 Hz to 18 kHz                       |
| Directivity               | Uni-directional                       |
| Sensitivity *[1]          | -31.0 dB $\pm$ 3.0 dB                 |
| Output Impedance *<br>[2] | 1.4 k $\Omega$ $\pm$ 30% (unbalanced) |

|   |                   |
|---|-------------------|
| Dynamic Range (typ.)                            | 94 dB or more     |
| Signal-to-Noise Ratio (typ.) * [3]              | 68 dB or more     |
| Inherent Noise (typ.) * [4]                     | 26 dB SPL or less |
| Maximum Input Sound Pressure Level (typ.) * [5] | 120 dB SPL        |

## General Section

|   |   |
|---|---|
| Mic Cable                               | 1.2 m (3.9 feet)  |
| Power Requirements                      | DC 1.5 V to 10 V  |
| Dimensions * [6]                        | 15 diameter (capsule case) x 25 mm (19/32 diameter x 1 inch)    |
| Mass (microphone body, excluding cable) | 5 g (0.18 oz) without connector                                 |
| Supplied Accessories                    | Mic holder clip (1), Windscreen (1), Operating instructions (1) |
| Optional Accessories                    | Mic holder clip SAD-HZ1B, Windscreen AD-RX7B                    |

## Notes

Notes

\*[1] 0 dB = 1 V/Pa, at 1 kHz

\*[2] Output impedance at 1 kHz

\*[3] A-weighted, 1 kHz, 1 Pa.

\*[4] 0 dB SPL = 20  $\mu$ Pa.

\*[5] 0 dB SPL = 20  $\mu$ Pa.

\*[6] The values for dimensions are approximate.

---

## Gallery

