

HDC-5500V

2/3-inch 4K 3-CMOS sensor portable system camera



NETWORKED **LIVE**

Specifications

General

Power requirements	AC 240 V, 1.4 A (max.), DC 12 V, 9.5 A (max.), DC 240 V, 1.05 A (max.)
Operating temperature	-20°C to +45°C (-4°F to 113°F)
Storage temperature	-20°C to +60°C (-4°F to +140°F)
Dimensions (W x H x D)	138 x 268 x 368 [Hood is not included.]
Weight	Approx. 5.1 kg (11 lb 3.9 oz) (unit only)

Imager

Imager	2/3 inch type 4K CMOS sensor with global shutter
Method	3-CMOS, RGB
Effective resolution (H x V)	QFHD: 3840 × 2160 HD: 1920 × 1080

Electrical characteristics

Sensitivity	F10 with 1080/59.94p F11 with 1080/50p (at 2000 lx with 89.9% reflectance)
Signal-to-noise ratio	-62 dB
Geometric distortion	Negligible (not including lens distortion)

Optical system specifications

Spectrum system	F1.4 prism
Built-in filters	ND filters 1: CLEAR, 2-5: Variable ND (1/3-1/256) CC filters A: Cross filter, B: 3200K (clear), C: Black mist*2, D: Extra Optical low pass filter

Input/output connectors

CCU	Optical/electrical multi connector (LEMO 3K.93C connector) (x1)
LENS	12-pin (x1)
VF	20-pin (x1)
Audio input	MIC 1 IN : XLR 3-pin, female (x1) AUDIO IN CH1, CH2 : XLR 3-pin, female (x1 each) When AUDIO switch is set to MIC: -60 dBu (can be selected up to -20 dBu by menu operation), balanced When AUDIO switch is set to LINE: 0 dBu, balanced
INTERCOM	INTERCOM 1, INTERCOM 2 : XLR 5-pin, female (x1 each)
EARPHONE	4-pole mini jack (x1), (3-pole stereo, 4-pole CTIA standard, 4-pole OMTP standard)
DC IN	XLR 4-pin (x1), DC 10.5 to 17 V
DC OUT	4-pin (x1), DC 10.5 to 17 V, max. 0.5 A* ¹ 2-pin (x1), DC 10.5 to 17 V, max. 2.5 A* ¹
SDI	SDI 1 : BNC (x1) SDI 2 : BNC (x1)
SDI MONI	BNC (x1)
TEST OUT	BNC (x1)
PROMPTER/GENLOCK	BNC (x1) PROMPTER 1 Vp-p, 75 Ω GENLOCK HD: SMPTE ST274, tri-level sync, 0.6 Vp-p, 75 Ω, SD: Black burst (NTSC: 0.286 Vp-p, 75 Ω/PAL: 0.3 Vp-p, 75 Ω)
PROMPTER2	No
RET CTRL	6-pin (x1)
REMOTE	8-pin (x1)
TRACKER	12-pin (x1)
CRANE	12-pin (x1)
USB	USB 2.0 Type A 4-pin (x1) (for connecting USB drive)
NETWORK TRUNK	RJ-45 type 8-pin (x1)

Supplied accessories

Supplied accessories

Before Using This Unit (1),
Operating Instructions (CD-ROM) (1),
Cable clamp belt (1 set),
Screws (+B3×8) (2),
Attached label (1)

Note

*1

This may be limited by the imposed load or inputs.

*2

Replacing Black mist filter as standard from the unit shipped out after October, 2024. For details, please contact sales in your region.

Related products



RCP-3500

Remote-control panel for HDC/HSC/HXC series cameras



RCP-3100

Joystick type of remote control panel for HDC/HSC/HXC series cameras.
5 units in 19-inch EIA rack.



RCP-1000

Joystick type of simple Remote Control Panel for HDC/HSC/HXC series cameras.6 units in 19-inch EIA rack.



MSU-3500

Master setup unit, multi camera remote control panel for system cameras (vertical type)



MSU-3000

Master setup unit, multi camera remote control panel for system cameras (horizontal type)



HKC-TR37

Digital Triax Transmission Adaptor for HDC camera series



HKC-WL50

Wireless transmission adaptor for HDC-5500 and HDC-3500




HKCU-REC55

Recording option for HDCU-5500 and HDCU-3500 CCU



HKCU-REC50

Recording option for HDCU-5000



HKCU-UHF50

4K 4x processor board for HDCU-5000



Color Calibrator

Fine tune colour reproduction for your virtual production



Camera and Display Plugin

Design, visualise and refine your virtual production shots



© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.