

SNCA-POLE30

Mounting pipe for pendant mount applications



Overview

Applicable Housing Models;

- SNCA-HRX550/EXT
- SNCA-HRX550/EXT/W
- SNCA-HRX550/INT
- SNCA-HRX550/EXT/R
- SNCA-HRX550/EXT/PRE
- SNCA-HRZ50/EXT
- SNCA-HRZ50/EXT/W
- SNCA-HRZ50/INT
- SNCA-HRZ50/EXT/R

Optional accessories;

- SNCA-CEILING (Ceiling Mount Adapter)

Related products



SNC- EB600

Box-type 720p/30 fps
Camera Powered by
IPELA ENGINE EX™ - E
Series



SNC- EB600B

Basic Box-type
720p/30 fps Camera
Powered by IPELA
ENGINE EX™ - E Series



SNC- EB630

Box-type 1080p/30 fps
Camera Powered by
IPELA ENGINE EX™ - E
Series



SNC- EB630B

Basic Box-type
1080p/30 fps Camera
Powered by IPELA
ENGINE EX™ - E Series



SNC- VB600

Box-type 720p/60 fps
Camera Powered by
IPELA ENGINE EX™ - V
Series



SNC- EP521

Standard Definition
(PAL) PTZ Network
Camera



SNC- EP580

1080p/30 fps PTZ
Camera - E Series



SNC- ER521

Standard Definition
(PAL) Rapid Dome
Network Camera



SNC- ER550

720p/30 fps Rapid
Dome Camera - E
Series



SNC- ER580

1080p/30 fps Rapid
Dome Camera - E
Series



SNC- ER585

Outdoor Unitized
1080p/30 fps Rapid
Dome Camera - E
Series

Gallery

