

CNU-700//U

Camera command network unit



Overview

*High-speed data transmission rates - more than 500 kb/s between CNU and MSU/RCP/CCU and 35 kb/s between camera head and CCU. Expandable system configuration - up to 12 cameras with one CNU-700 and one BKP-7930 installed. Character display function in monochrome. Bypass facility to maintain communication between the CCUs and RCPs in the event of a CNU malfunction or power loss.

Specifications

General

Power requirements:	AC 100 to 120 V, 50/60 Hz (For USA and Canada) AC 220 to 240 V, 50/60 Hz (For other countries)
---------------------	--

Power consumption:	4.0 VA max.
--------------------	-------------

Operating temperature:	0 to +45 °C (+32 to +113 °F)
------------------------	------------------------------

Mass:	9.5 kg (20 lb 15 oz)
-------	----------------------

Dimensions:	424(W) x 132(H) x 400(D) mm (16 3/4
-------------	-------------------------------------

x 5 1/4 x 15 3/4 inches)

Input/output connectors

CCU 1 through 6: 8-pin multiconnector (1 each)

RCP 1 through 6: 8-pin multiconnector (1 each)

MSU: 8-pin multiconnector (1)

VCS: 8-pin multiconnector (1)

AUX 1 and 2: 8-pin multiconnector (1 each)

Character: BNC type (2) video: 0.7 Vp-p, sync:
0.3 Vp-p

Reference: BNC type (2) 0.3 Vp-p with loop-
through output

RS-232C D-sub 9-pin (3)

AC input: 3-pin (1)

Gallery

