

ECM-674

Affordable shotgun Electret condenser microphone



Overview

The ECM-674 is an affordable shotgun-type electret condenser microphone, which delivers excellent sound performance in field and studio productions.

Superb Sound Quality

The ECM-674 offers an excellent sensitivity of -36 dB (0 dB=1 V/Pa.) and low inherent-noise level of less than 17 dB SPL. This allows the microphone to be used for clear voice pick-up even in noisy environments

Two-way Powering

A two-way powering capability allows the ECM-674 to be driven by microphone power or batteries, making it suitable for both camcorder mounting and many other sound-gathering applications. Internal: AA-size battery operation. External: DC (40 to 52 V) operation

Built-in Battery Liquid Leakage Protection Circuit

In general, old batteries can leak and damage the equipment they are used in. The ECM-674 prevents this by continually detecting the output voltage of the battery and shutting off the power supplied to the electric circuit whenever the voltage drops beneath a certain threshold.

Features

Flat-and-wide Frequency Response

The ECM-674 microphone has a flat-and-wide frequency response (40 Hz to 20 kHz) and provides sound reproduction that is extremely smooth and natural

Compact and Lightweight Design

The ECM-674 has been designed as a highly directional compact and lightweight shotgun microphone. It measures only 268 mm (10 5/8 inches) in length and weighs just 185 g (6.5 oz), maintaining good balance even when mounted on compact camcorders.

Built-in Low Cut Filter

The built-in two-position (M, V) low-cut switch provides users with a simple method of reducing the effects of undesired ambient noise.

Specifications

Audio Section

Capsule Type	Mono Electret Condenser
Frequency Response	40 Hz to 20 kHz

Directivity	Uni-directional (super-cardioid)
Sensitivity *[1]	-36 dB ±3 dB
Output Impedance *[2]	220Ω±20%, Balanced
Dynamic Range	Phantom: 107 dB or more Battery: 98 dB or more
Signal-to-Noise Ratio *[3]	77 dB or more
Inherent Noise *[4]	17 dB SPL or less
Induction Noise From External Magnetic Field *[5]	0 dB SPL or less
Wind Noise *[6]	50 dB SPL (without windscreen) 45 dB SPL or less (with windscreen)
Maximum Input Sound Pressure Level *[7]	Phantom: 124 dB SPL Battery: 115 dB SPL

General Section

Connector	XLR-3-12C (male)
Mic Cable	XLR-3 to XLR-3 500 mm 19.6 inches
Power Requirements	External: DC 40 V to 52 V Battery: 1.5 V
Dimensions *[8]	φ20 x 268 mm φ13/16 x 10 5/8 inches
Mass	Approx. 7.3 oz with battery Approx. 6.5 oz without battery Approx. 208 g with battery Approx. 185 g without battery
Supplied Accessories	Windscreen (1) Stand adaptor (2) Short XLR cable Operating instructions (1) Mic spacer (2) Mic holder (1)

Notes

Note	<p>*[1] 0 dB = 1 V/Pa, at 1 kHz *[2] Output impedance at 1 kHz *[3] A-weighted, 1 kHz, 1 Pa. *[4] 0dB SPL = 20? Pa. *[5] dB SPL/1E-7 T, 0 dB SPL = 20? Pa. *[6] Wind noise at 2m/s (0 dB SPL = 20?Pa.) *[7] 0 dB SPL = 20? Pa. *[8] The values for dimensions are</p>
------	--

approximate.

Related products



HXC-FB80

Three 2/3-inch Exmor™ CMOS
sensor HD colour studio
camera

Gallery

