

FWD-55X81CH

X81CH Series 4K HDR LED TV



Overview

Vivid, colourful 4K HDR pictures and sound that surrounds you

The BRAVIA FWD-55X81CH brings you the clarity, colour and contrast of 4K plus rich multi-dimensional sound, framed in a slim, luxurious design.

Our power-packed X1 processor boosts image detail and cuts noise, bringing you spectacular 4K HDR images that bring you closer to reality. Even lower-resolution pictures are upscaled close to 4K resolution, bringing greater clarity to everything you're viewing or presenting.

Our BRAVIA Professional Displays surrounds you with pure sound that pulls you right into the scene. With Dolby Atmos, sound comes from above as well as from the sides so you can hear objects moving overhead with more realism for a truly multi-dimensional experience.

The FWD-55X81CH blends harmoniously with any contemporary interior. The displays slim blade design is complemented by a narrow screen bezel that adds an extra touch of refinement.

The BRAVIA FWD-55X81CH is ideally suited to professional use, with Pro mode allowing quick and easy customisation to suit

different environments. Android TV lets you do more, with the display's intuitive built-in software platform broadening control and customisation options even further. Creating attractive digital signage is simple, mixing and displaying media files and online content with no need for additional hardware. A wide range of APIs (Application Programming Interface) options enable remote control/monitoring and integration with external systems.

Features

4K image resolution (3840 x 2160 pixels)

4K offers four times the detail of Full HD, with a resolution of over 8 million pixels bringing extra clarity to corporate display, education and digital signage applications.

More contrast, colour and clarity

Our 4K HDR Processor X1™ cleans and refines picture signals, using advanced algorithms to cut noise and boost detail. Even lower-resolution images are upscaled closer to 4K with lifelike colour and textures.

See finer detail

4K X-Reality PRO upscales pictures closer to true 4K quality.

Images are sharpened and refined in real time, revealing extra detail from lower-resolution picture sources.

Powered by our X1 processor, TRILUMINOS Display maps colours from a wider palette, faithfully reproducing a world of more vivid, lifelike hues and tones.

Wider colour with TRILUMINOS Display

Powered by our X1 processor, TRILUMINOS Display maps colours from a wider palette, faithfully reproducing a world of more vivid, lifelike hues and tones.

Less blur, even in fast scenes

Motionflow technology keeps on-screen movement smooth and

clear by creating extra images between images and black segments between scenes. You'll see the difference with reduced blur more natural, flowing motion.

Refined style to match your space

BRAVIA features a slim, contemporary blade design, with a narrow screen bezel that adds an extra touch of refinement to any interior.

Do more with Android TV

Discover a world of apps and online content powered by Android. Use Voice Search to find content easily without typing. Easily share content with Google Cast.

Works with Apple AirPlay

With Apple AirPlay it's easy to stream video and sound to BRAVIA right from an iPhone, iPad or Mac.

Google Chromecast built in

Cast videos and apps from a mobile device directly to BRAVIA with Google Chromecast. Just tap the Cast button on your Android or iOS device screen and instantly enjoy super-sized on BRAVIA.

Quick set-up with Pro Mode

Customise and store display settings and features, then copy easily to multiple displays via USB flash memory.

Easily create digital signage

Integrated support for HTML5 makes it easy to produce compelling digital signage. Combine graphics, text, video and live web content to create attractive signage in minutes with no extra hardware or special training.

Versatile remote control

Control BRAVIA remotely – including on/off, input signal select and adjust volume – over IP via RJ45 by web API.

Specifications

TV System

Tuner Channel Coverage (Analog)	VHF: 2-13/UHF: 14-69/CATV: 1-135
---------------------------------	----------------------------------

Tuner Channel Coverage (Digital Terrestrial)	VHF: 2-13/UHF: 14-69
--	----------------------

Tuner Channel Coverage (Digital Cable)	CATV: 1-135
--	-------------

Number of Tuners (Terrestrial/Cable)	1(Digital/Analog)
--------------------------------------	-------------------

TV System (Analog)	M
--------------------	---

Voice Remote Control	RMF-TX500U
----------------------	------------

Batteries	LR03
-----------	------

TV System (Digital Terrestrial)	ATSC
---------------------------------	------

TV System (Digital Cable)	Clear QAM
---------------------------	-----------

Auto Mute (on no signal)	Yes(Audio only)
--------------------------	-----------------

Display Features

Display type	LCD
Backlight type	Direct LED
Backlight dimming type	Frame Dimming
Panel Refresh Rate (Native Hertz)	60Hz
PhotoTV HD / BRAVIA 照片秀 for China	Yes
Auto Picture Mode	Yes
Color Space	sRGB,BT709,BT2020,AdobeRGB,DCI
Color System	NTSC
Demo Mode	Yes(e-POP only)
4K Processor	4K HDR Processor X1

Video Specs

Auto Wide	Yes
Wide Mode	Auto/Wide Zoom/Normal/Full/Zoom Normal/Full1/Full2 for PC

4:3 Default	Yes
Video Processing	4K X-Reality PRO
Motion enhancer	Motionflow XR 240 (Native 60Hz)
CineMotion/Film Mode/Cinema Drive	Yes
24p True Cinema	Yes

Audio Specs

Speaker Configuration	Full Range (Bass Reflex) (35 x 85mm) x 2
Speaker Position	Down Firing
Channel	2ch
Speaker Type	Bass Reflex Speaker
Speaker Type-2	X-Balanced Speaker
Audio Power Output	10W + 10W

Network Specs

Wi-Fi Direct	Yes
Wi-Fi Certified	Yes

Screen

mirroring(Miracast™)	Yes (only for B2B purpose)
Internet Browser	Vewd (Not pre-installed)
Wireless LAN	Integrated
Wi-Fi Standard	a/b/g/n/ac
Wi-Fi Frequency	2.4GHz/5GHz (for Wi-Fi Direct: 2.4GHz Only)
Bluetooth profile support	Version 4.2
Bluetooth profile support	HID/HOGP/SPP

Convenience Features

USB playback codecs	MPEG1:MPEG1/MPEG2PS:MPEG2/MPEG2TS(HDV,AVCHD):AVC,MPEG4,HEVC/AVI:Xvid,MotinJpeg/ASF(WMV):VC1
USB drive format support	Yes (Supported File System: FAT16/FAT32/exFAT/NTFS)
Voice Search	Yes
Application Store	Yes (Google Play Store)

On Screen Clock	Yes
Sleep Timer	Yes
On/Off Timer	Yes
Display Language	AFR,AMH,ARA,ASM,AZE,BEL,BUL,BEN,BOS,CAT,CZE,DA,SWA,TAM,TEL,THA,TGL,TUR,UKR,URD,UZB,VIE,zh_CN,
On-board Storage (GB)	16GB
Text Input Language	ENG / FRA / GER / HEB / ITA / RUS / SPA / VIE / JPN
Operating Instructions	US,FR
Quick Setup Guide / Supplement CUE (GA)	US,FR,ES,PT
Codec for Home Network	MPEG1:MPEG1/MPEG2PS:MPEG2/MPEG2TS(HDV,AVCHD):AVC,MPEG4,HEVC/AVI:Xvid,MotinJpeg/ASF(WMV):VC

Inputs and Outputs

HDCP	HDCP2.3(for HDMI1/2/3/4)
RF (Terrestrial/Cable) Connection Input(s)	1(Side)
Composite Video Input(s)	1(Side)
HDMI inputs total	4(4Side)
Analog Audio Input(s) (Total)	1(Side Analog Conversion)
Digital Audio Output(s)	1(Side)
Headphone Output(s)	1(Side)
USB ports	2(Side)
Ethernet inputs	1(Side)
RS-232C Input(s)	1(Side)
RS-232C Control	Yes
Video & TV SideView (iOS/Android)	Yes
Chromecast built-in	Yes
Apple AirPlay	Yes
Apple HomeKit	Yes

HDMI input Audio format	5.1 channel linear PCM: 32/44.1/48/88.2/96/176.4/192kHz 16/20/24bits, Dolby Audio, Dolby Atmos, DTS
-------------------------	---

HDMI Audio Return Channel(ARC)	Yes (ARC) (for HDMI3)
--------------------------------	-----------------------

HDMI-CEC	Yes
----------	-----

Design Features

Bezel Design	Narrow Bezel
--------------	--------------

Frame color	Black
-------------	-------

Table Top Stand	Separate(assembly required)
-----------------	-----------------------------

VESA® Hole Spacing Compatible	Yes
-------------------------------	-----

Stand Design	Slim Blade Stand
--------------	------------------

Stand Color	Silver
-------------	--------

VESA® Hole Pitch(W x H)	300 x 300 mm / 11 7/8 x 11 7/8 inch
-------------------------	-------------------------------------

Eco and Energy Saving

Screen Size (inch, measured diagonally)	55"(54.6")
---	------------

Screen Size for WEB (diagonal, cm, integer or 1st decimal)	139 cm
Rated Power Consumption	196 W
Power Consumption (in Standby)	0.5 W
Annual Power Consumption	161 kWh/Year
Power Requirements (voltage)	AC 120V for UL cUL AC 110-240V for other
Power Requirements (frequency)	60Hz for UL cUL 50/60Hz for other
Power Saving Mode / Back Light Off Mode	Yes
Dynamic Backlight Control	Yes
Dynamic Contrast Enhancer	Yes
Sensor	Light
AC Power Input	C8 INLET(REAR)

Measurements

Dimension of TV
without Stand (W x H x D) 1243 x 718 x 71 (16) mm

Dimension of TV with
Stand (W x H x D) 1243 x 782 x 340 mm

Dimension of Package
Carton (W x H x D) 1348 x 833 x 160 mm

Stand Width 979 mm

Weight

Weight of TV without
Stand 16.0 kg

Weight of TV with
Stand 16.8 kg

Weight of Package
Carton (Gross) 22 kg

Max Qty of carton
stacking (vertical) 6

Max Qty of carton
stacking (horizontal) 0
*only for Shop Front

Display Specifications

Viewing Angle (Right/Left)	178(89/89) degree
-------------------------------	-------------------

Viewing Angle (Up/Down)	178(89/89) degree
----------------------------	-------------------

Display Resolution	QFHD
--------------------	------

Display resolution (H x V, pixels)	3840x2160
------------------------------------	-----------

Aspect Ratio	16:9
--------------	------

Operating System	Android 9.0 Pie
------------------	-----------------

Control Specs

Pro Mode	Yes
----------	-----

IP control	Yes
------------	-----

HDMI out wake-up	Yes
------------------	-----

HDR (High Dynamic Range) compatibility	Yes(HDR10,HLG,Dolby Vision)
--	-----------------------------

Power Saving Mode / Back Light Off Mode	Yes
---	-----

Auto Shut-off	Yes
---------------	-----

Audio Power Output	10W + 10W
Auto Surround	Yes
S-Master	S-Master Digital Amplifier
Dolby audio format support	Dolby Audio, Dolby Atmos
Dolby Atmos	Yes
DTS audio format support	DTS Digital Surround
Advanced Auto Volume	Yes
Bass/Treble/Balance	Balance
Digital audio out (Optical) format	Two channel linear PCM: 48kHz 16bits, Dolby
ARC output format	Two channel linear PCM: 48kHz 16bits, Dolby Atmos, DTS
Clear Phase	Yes
Show/Hide Channels	Yes(Digital&Analog)
Channel Block (with password)	Yes(Analog&Digital)
Hotel Mode Menu	Yes

Electronic Program Guide (EPG)	Yes
Related Info	Yes (US / Canada / MX(STB))
Home Network Feature	Home Network Client, Home Network Rende
Parental Control	Yes
Closed Captions (Analog)	
Closed Captions (Digital)	
Auto Calibration with CalMAN	Yes
Screen Reader	Yes
Audio Description	Yes
Text Magnification	Yes
Accessibility Shortcut	Yes
Switch Access	Yes
4K 60P High-Quality formats	HDMI IN1, IN2, IN3, IN4 ports for 4K(up to 180
Cable Management	Yes

Gallery



