

## HZC-QFR50 / HZC-QFR50M / HZC-QFR50W

Max. HD 4x Slow motion with HDC-3500 system camera and others



### Overview

#### **Software licenses for shooting Max. HD 4x slow motion with HDC-3500 system camera and others**

HZC-QFR50, HZC-QFR50M and HZC-QFR50W are the software licenses on the HDC-3500 for shooting Max. HD 4x slow motion.

The HZC-QFR50 can be permanently used.  
The HZC-QFR50M can be used for 30 days.  
The HZC-QFR50W can be used for 7 days.

Activation key for pre-installed software.

### Related products



#### **HKC-WL50**

Wireless transmission adaptor for HDC-5500 and HDC-3500



#### **HDC-3500**

Three 2/3-inch 4K CMOS sensors portable system camera for fibre operation



#### **HDC-5500**

High performance three 2/3-inch 4K CMOS sensor portable system camera with direct 4K output



#### **HDC-P50**

4K/HD compact POV system camera

## Gallery

