

## PWA-RCT1/01

ISO record software for PWS-4500



### Overview

#### **ISO record software for PWS-4500**

##### **Highlights**

- 4K x 4 I/O (input/output software configurable) 4IN, 3IN/1OUT, 2IN/2OUT, 1IN/3OUT, 4OUT
- HD I/O up to 6IN/1OUT or 4IN/2OUT
- Video and audio format video: XAVC codec 4K XAVC-I (600Mbps @ 60p) HD XAVC-I (100Mbps @ 60i). Audio: LPCM 24-bit 16-Channels
- 4K recording, 4K up to 60fps, recording with PMW-F55 4K up to 120fps, recording with F65
- High frame rate HD 240p/360p/240i/360i, HFR recording with PMW-F55
- 4K for HD cut-out mode: HD cut-out mode allows the operator to generate HD output from a 4K image. It supports a touch-based interface with variable zoom and key frames.
- Network interface 2 x GbE ports are standard with a 10GbE port available as an option.
- RS-422 control Sony VTR/Disk, VDCP and Odetics protocols are supported.
- Internal memory storage (includes 2TB as standard), 5 hours @ 4K 60p (600Mb/s), 24 Hours @ HD 60i (100Mb/s). Expandable up to 8TB (additional PWSK-4401 memory boards sold separately)
- 4K stitch support: With a single PWS-4400, it is possible to record and play back two 4K signals. This makes it perfect for the Sony

PWA-4KS 4K Stitch application. 4K Stitch combines the output of two 4K cameras to create an 8K x 2K video canvas. Up to three virtual HD cameras can be derived using this technology with full pan, scan and zoom capabilities.

## Related products



### **PWAL- RCT50**

CCU recording control option for PWA-RCT1

## Gallery

