

## SNCA-CEILING

Mounting coupling for pendant applications



### Overview

Features;

- The coupling is mounted to the ceiling. SNCA-POLE30 is threaded into the coupling and the camera housing connected to the bottom of the pipe.
- The base has an input for electrical conduit (1/2" or 12.7 mm)

### Related products



#### **SNC-EB600**

Box-type 720p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



#### **SNC-EB600B**

Basic Box-type 720p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



#### **SNC-EB630**

Box-type 1080p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



#### **SNC-EB630B**

Basic Box-type 1080p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



#### **SNC-VB600**

Box-type 720p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



#### **SNC-EP521**

Standard Definition (PAL) PTZ Network Camera



#### **SNC-EP580**

1080p/30 fps PTZ Camera - E Series



#### **SNC-ER521**

Standard Definition (PAL) Rapid Dome Network Camera



## **SNC- ER550**

720p/30 fps Rapid  
Dome Camera - E  
Series



## **SNC- ER580**

1080p/30 fps Rapid  
Dome Camera - E  
Series



## **SNC- ER585**

Outdoor Unitized  
1080p/30 fps Rapid  
Dome Camera - E  
Series

## Gallery

