

## HDCAM

This sophisticated format offers prestige HD quality at remarkable cost, making it ideal for shooting drama, documentaries, commercials and mainstream television programming.



### Overview

#### **HDCAM**

- Continually-developed metal tape technology
- Strengthened binder achieves 50% increase in cross-linking density
- Dropout prevention and archival stability using alumina-silica particle coating
- Extended head life with specially developed lubricants
- Controlled surface roughness increases S/N ratio
- Cleaning Tape: BCT-5CLN

\* Product assortment may vary by region. Please consult your local Sony Account Representative.

### Specifications

#### General Characteristics

	BCT-124HDL: 10
	BCT-94HDL: 10
	BCT-64HDL: 10
Master Carton	BCT-34HDL: 10

Quantity (piece)	BCT-40HD: 50
	BCT-32HD: 50
	BCT-22HD: 50
	BCT-6HD: 50
Master Carton Weight (kg)	BCT-124HDL: 8.3
	BCT-94HDL: 7.8
	BCT-64HDL: 7.3
	BCT-34HDL: 6.8
	BCT-40HD: 17.3
	BCT-32HD: 16.7
	BCT-22HD: 15.8
BCT-6HD: 14.9	
Playing time (min)	BCT-124HDL: 124
	BCT-94HDL: 94
	BCT-64HDL: 64
	BCT-34HDL: 34
	BCT-40HD: 40
	BCT-32HD: 32
	BCT-22HD: 22
BCT-6HD: 6	
Tape length (m)	BCT-124HDL: 732
	BCT-94HDL: 557
	BCT-64HDL: 382
	BCT-34HDL: 206
	BCT-40HD: 241
BCT-32HD: 195	
BCT-22HD: 136	

	BCT-6HD: 43
Weight (g)	BCT-124HDL: 780
	BCT-94HDL: 728
	BCT-64HDL: 677
	BCT-34HDL: 630
	BCT-40HD: 308
	BCT-32HD: 295
	BCT-22HD: 277
	BCT-6HD: 260

## Magnetic Properties

Intrinsic coercivity (kA/m)	132.0
Retentivity (mT)	290.0
Squareness (Br/Bm)	0.83

## Physical Properties

Thickness: backcoating (μm)	1.0
Thickness: base (μm)	10.0
Thickness: magnetic layer (μm)	3.0

Thickness: total ( $\mu\text{m}$ )	14.0
------------------------------------	------

---

Width (mm)	12.65
------------	-------

---

## Video and Audio Performance

Recording Density (Mb/inch <sup>2</sup> )	0.0
--	-----

---

RF Playback output (dB)	0.0
----------------------------	-----

---

C/N	0.0
-----	-----

---

## Gallery

