

ODBK-202

*Please contact your local sales representative for details.



Overview

The ODBK-202 is a base unit of power supply for the ODS-L30M.

The ODBK-20X series can drive the ODS-D280F and the ODS-D77F.

A world of solutions

Related products



ODS-L30M

*Please contact your local sales representative for details.



ODS-L60E

*Please contact your local sales representative for details.



ODS-L100E

*Please contact your local sales representative for details.



ODS-D280F

Optical Disc Archive fibre channel drive unit for the ODS-L30M/L60E/L100E PetaSite scalable library with very high transfer speeds of 1Gbps write (verify on) and 2Gbps read using ODC-3300R Generation 2 cartridge

Gallery

