

UNI-OFL7T2

7-inch outdoor vandal-resistant tinted flush-mount housing with heater/blower for SNC-RH124, SNC-RS44N, SNC-RS46N, SNC-RX series and SNC-RZ25N PTZ cameras, AC 24V power



Overview

Outdoor vandal resistant flush mount enclosure with thermostatically controlled heater/ blower

The flush-mount 7-inch vandal resistant rugged housing offers versatility and camera protection in a compact size. These outdoor surface mount enclosures can be mounted facing down or facing up toward the sky. The housing is available with a tinted dome. AC 24V input is required for the heater.

Tinted dome

7-inch polycarbonate.

Features

Outdoor vandal resistant flush mount housing

7-inch tinted polycarbonate lower dome.

Thermostatically controlled heater and blower

AC 24V input.

Gallery

