

UNI-OPBC6

Pressurised temperature controlled vandal-resistant security camera housing



Overview

The UNI-OPBC6 is a pressurised tubular vandal-resistant fixed camera housing that's compatible with Sony SNC-EB6xx and SNC-VB6xx box-type security cameras.

The enclosure meets NEMA type 6P and IP67 standards for superior moisture, dust and dirt ingress protection. It's also IK10 impact rated. It features a Schraeder valve, allowing the housing to be filled with nitrogen or another clean, inert gas.

Stable operation in a climatic extremes is ensured by the integrated heater/blower and sunshield. Suitable for wall/pole mounting, the UNI-OPBC6 supports PoE with Dynamic Power Allocation (DPA), assuring optimum power delivery to the camera in all conditions. In addition, PoE+ IEEE802.3at support allows powering from a single cable.

Related products



SNC-EB600

Box-type 720p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



SNC-EB600B

Basic Box-type 720p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



SNC-EB630

Box-type 1080p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



SNC-EB630B

Basic Box-type 1080p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



SNC- EB640

Box-type Full HD IP
Network Camera (E-
Series)



SNC- VB600

Box-type 720p/60 fps
Camera Powered by
IPELA ENGINE EX™ - V
Series



SNC- VB600L

Box-type 720p/60 fps
Camera Powered by
IPELA ENGINE EX™ - V
Series



SNC- VB630

Box-type 1080p/60 fps
Camera Powered by
IPELA ENGINE EX™ - V
Series



SNC- VB635

Box-type 1080p/60 fps
Camera with Half-inch
Exmor™ CMOS Sensor
Powered by IPELA
ENGINE EX™ - V Series



SNC- VB640

Box-type Full HD
1080p/60fps IP
Network Camera (V-
Series)

Gallery

