

UNI-OTBC2

Temperature-controlled vandal resistant outdoor security camera housing



Overview

This vandal-resistant housing is compatible with Sony SNC-EB6xx and SNC-VB6xx series box-type security cameras.

Suitable for wall or pole mounting outdoors, the UNI-OTBC2 meets NEMA Type 4 and IP66 standards for resistance to dust/moisture penetration. It's also IK10 impact rated.

Ideal for use in a wide range of climatic environments, the camera housing features an adjustable sunshield plus a thermostatically controlled heater and fan cooling system.

Operating voltage 24V AC or 12V DC.

Related products



SNC-EB600

Box-type 720p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



SNC-EB600B

Basic Box-type 720p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



SNC-EB630

Box-type 1080p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



SNC-EB630B

Basic Box-type 1080p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



SNC- EB640

Box-type Full HD IP
Network Camera (E-
Series)



SNC- VB600

Box-type 720p/60 fps
Camera Powered by
IPELA ENGINE EX™ - V
Series



SNC- VB600L

Box-type 720p/60 fps
Camera Powered by
IPELA ENGINE EX™ - V
Series



SNC- VB630

Box-type 1080p/60 fps
Camera Powered by
IPELA ENGINE EX™ - V
Series



SNC- VB635

Box-type 1080p/60 fps
Camera with Half-inch
Exmor™ CMOS Sensor
Powered by IPELA
ENGINE EX™ - V Series



SNC- VB640

Box-type Full HD
1080p/60fps IP
Network Camera (V-
Series)

Gallery

