

## DSRM-10

Remote control unit



### Overview

Provides wired remote control operation for STOP/REC/PAUSE/REW/PLAY/FFWD. JOG/SHUTTLE operation. Enables  $\pm 16$  times normal speed in search operation

### Specifications

#### Generic Specifications

|                    |  |
|--------------------|--|
| Power requirements | DC 5 V (supplied from the connected VTR)                       |
| Power consumption  | 50 mW  |
| Remote control     | Stereo mini-plug (with attached cable, length 3 m (10 ft))     |
| Dimensions         | 90 (W) × 46 (H) × 182 (D) mm, (3 5/8 × 1 13/16 × 7 1/4 inches) |
| Mass               | Approx. 360 g (12 oz)  |

## Gallery

