

SNC-UNI

Indoor fixed camera housing



Overview

13-inch indoor aluminium housing with clear window and hinged opening

Tamper resistant camera housing with lock down screws provided. High strength steel wall mount bracket included.

Flexible positioning

Designed for mounting to a flat wall or round pole, larger than 3.5 inches in diameter.

Features

Flexible positioning

Designed for mounting to a flat wall or round pole, larger than 3.5 inches in diameter.

Supports a variety of cameras

Network cameras accepted: SNC-CH120/140/220/240, SNC-ZB550, and SNC-EB520. analogue cameras accepted: SSC-FB530/560, SSC-G113A/213A and SSG-G103A/203A. Maximum camera/lens length should not exceed 9.5 inches.

Related products



SNC- VB635

Box-type 1080p/60 fps
Camera with Half-inch
Exmor™ CMOS Sensor
Powered by IPELA
ENGINE EX™ - V Series



SNC- VB630

Box-type 1080p/60 fps
Camera Powered by
IPELA ENGINE EX™ - V
Series



SNC- VB600

Box-type 720p/60 fps
Camera Powered by
IPELA ENGINE EX™ - V
Series

SNC- EB600

Box-type 720p/30 fps
Camera Powered by
IPELA ENGINE EX™ - E
Series

SNC- EB630

Box-type 1080p/30 fps
Camera Powered by
IPELA ENGINE EX™ - E
Series

SNC- EB520

Box-type SVGA
Camera - E Series

Gallery

