

## UHC-8300

UHC-8300 8K 3CMOS sensor

Camera system includes UHCU-

8300 8K Camera Control Unit,

UKCU-8001 (8K ST 2110

Interface), UZCU-SNMP80 (SNMP

for 8K ST 2110), UKCU-IP01F

(Networked Media Interface)



**NETWORKED LIVE**

### Overview

#### **A new landmark in broadcasting in 8K**

The world's first 8K television channel is already on air in Japan. And Sony is proud to be supporting this broadcasting landmark with the UHC-8300 system camera that enables an entire 8K Ultra HD workflow – from image capture to storage, editing, display and playout. The Sony 8K camera system consists of the combination of UHC-8300 camera head and UHCU-8300 camera control unit.

#### **Perfection in every detail**

At the heart of the UHC-8300 is the world's first 1.25-type 8K 3CMOS sensor, capturing pristine images with a resolution of 7680x4320 pixels and a signal to noise ratio of -62dB (at 1080/59.94i). It realizes the 8K picture capturing at high speed of 120p HDR. Along with this new generation image sensor, the newly developed F1.6 prism system is capable to support the BT.2020 wide colour space, allowing content creators to realise 8K images with unprecedented clarity, colour and realism. The 4K signal dot-by-dot extracted from 8K captured image can be utilized for the monitoring in accurate focusing camera operation without any degradation.

#### **8K adding more value to 4K production**

8K Ultra HD images captured with the UHC-8300 camera system can be downconverted to produce spectacular 4K UHD images, bursting with fine detail and colour. This allows content creators to add value to every production, ensuring that premium footage captured in 8K can be enjoyed by consumers on today's 4K HDR televisions and display devices. 8K images captured with the UHC-8300 can be enjoyed with native 7680x4320 pixel resolution on Sony's Crystal LED large-scale display system.

## **IP solutions for 8K system**

In addition to the NMI (Networked Media Interface Board): UKCU-IP01F, the 8K ST 2110 Interface Board: UKCU-8001 is available as an option product which works with LSM (Sony IP Live System Manage). The networked 8K ST 2110 system can be monitored by another license key option of SNMP: UZCU-SNMP80.

## Features

### **Advanced 8K interface**

Weighing just 7kg (approx.), the compact UHC-8300 camera head connects via a SMPTE fibre connection to the UHCU-8300 Camera Control Unit. The CCU outputs 8K 120p baseband signals over octal 12G-SDI based on SMPTE ST.2082-12. In parallel, simultaneous 4K and HD outputs are available over 12G/3G-SDI.

### **Made for tomorrow's workflows**

You're covered for today's production workflows as well as tomorrows. 8K Ultra HD images captured with the UHC-8300 can be stored and replayed as XAVC files using Sony's PWS-4500 live server. Also, the 8K signal can be transmitted to Sony's XVS-8000/9000 switcher, and combined with Sony's IP converters. And with a growing choice of third-party display, switching and editing solutions already available from Sony and other manufacturers, the 8K Ultra HD ecosystem is growing fast.

### **Simultaneous 8K/4K/HD production in HDR and**

## **SDR**

Teamed with the UHCU-8300 Camera Control Unit, the UHC-8300 enables HDR production workflows with a choice of S-Log3, HLG Live and HLG BT.2100. Broadcasters can also enjoy the benefits of Sony's SR Live, with simultaneous output of 8K, 4K and HD signals in HDR and SDR to suit a wide range of live production requirements.

## **New 8K lens mount**

A new 1.25-type lens mount system offers direct compatibility with specially developed 8K lenses from lens vendors. Current 4K lenses can also be used with a 1.25-type B4 lens mount adaptor.

## **Compatibility with current live production elements**

The UHC-8300 is compatible with current Sony live production system components including remote controllers, multi camera system units and viewfinders. So broadcasters and programme makers can realise fresh value from the current 4K/HD investments – today and tomorrow.

## **Real-time 4K cutout**

The extraordinary resolution of 8K UHD allows production teams to select a 4K cutout from a portion of images captured with the UHC-8300. Displayed on a 4K monitor, this allows critical inspection and confirmation of focus. This can be done by dot-by-dot extraction from the captured 8K image without any degradation.

## **IP solutions**

The IP based network connection makes much advanced flexible total system, and it can be realized even in 8K world. The 8K ST 2110 interface board, UKCU-8001 is optionally available. It can be monitored by SNMP activated with a license key of UZCU-SNMP80. An NMI (Networked Media Interface board), UKCU-IP01F option product is also available. Either IP board can be installed

to the CCU, UHCU-8300.

## Specifications

### UHC-8300 Camera Head General

Power Requirement and Consumption Current	240Vdc, 1.0A (max.) 12Vdc, 9.5A (max.)
---	---

Operating Temperature	-20°C to +45°C -4°F to +113°F
--------------------------	----------------------------------

Storage Temperature	-20°C to +60°C -4°F to +140°F
---------------------	-------------------------------

Dimensions (W x H x D)*1	167 x 299 x 396 mm
	6 5/8 x 11 7/8 x 11 3/4 inches

\*1 The values for dimensions are approximate and excluding the protrusions.

Mass	(Body) Approx. 7.0 kg
	(Body) Approx. 15 lb 7 oz

### UHC-8300 Camera Head Camera Section

Pickup Device	3-chip 1.25-inch type CMOS
---------------	----------------------------

Resolution	8K: 7680 x 4320 (H x V)
------------	-------------------------

Spectrum System	F1.6 prism system
-----------------	-------------------

Lens Mount	1.25-inch type bayonet mount,
------------	-------------------------------

LENS MOUNT	ARIB TR-B37
Built-in Filters	CC: A; 3200K(Clear), B; 4300K, C; 6300K, D; Cap ND: 1; Clear, 2; 1/4ND, 3; 1/16ND, 4; 1/64ND
Sensitivity (at 2000 lx, 3200K, 89.9% reflectance)	F8 (8K 59.94p), F9 (8K 50p)
Noise Level	-62dB (1080/59.94i)
Horizontal Resolution (8K: Center of the picture at Modulation depth 5% or higher.)	3,840 TV lines
Gain	-6, -3, 0, 3, 6, 9, 12 dB
Shutter Speed	1/100, 1/125, 1/250, 1/500, 1/1000, 1/2000 sec (59.94 mode) 1/60, 1/125, 1/250, 1/500, 1/1000, 1/2000 sec (50 mode)

## UHC-8300 Camera Head Input/Output

CCU	Optical/electrical multi-connector (x1)
Lens	12-pin (x1)

Viewfinder	20-pin (x1), for HDVF
Audio Input (CH1)	XLR type: 3-pin, female (x1) MIC IN: -60dBu (Up to -20dBu can be set by using menu or UHCU-8300), balanced LINE IN: +4dBu, balanced
Audio Input (CH2)	XLR type: 3-pin, female (x1) MIC IN: -60dBu (Up to -20dBu can be set by using menu or UHCU-8300), balanced LINE IN: +4dBu, balanced
Intercom	1: XLR type 5-pin, female (x1) 2: XLR type 5-pin, female (x1)
Earphone Output	Stereo mini jack (x1)
DC Input	XLR-type 4-pin (x1), DC 10.5 V to 17 V
DC Output	4-pin (x1), DC 10.5 V to 17 V (max. 0.5A)*2 2-pin (x1), DC 10.5 V to 17 V (max. 2.5A)*2  *2 May be limited, depending on load and input conditions.
	BNC (x1) SMPTE ST2082-10 12G-

SDI 1 Output	SDI Out, ST424/425-1 3G-SDI Out, ST292-1 HD-SDI Out or HD Prompter Out selectable
SDI 2 Input/Output	BNC type (x1) SMPTE ST292-1, HD-SDI Out or HD Video Trunk In selectable
Monitor Output	BNC (x1) SMPTE ST292-1, HD-SDI Out
SYNC Output	BNC (x1) HD-Sync, SD-Sync Out
Prompter Output	BNC (x1) 1Vp-p, 75Ω
Return Control	6-pin (x1) for CAC-6
For Future Use	8-pin (x1)
Tracker	10-pin (x1)
MAG Control	14-pin (x1)
Crane	12-pin (x1)
Network Trunk	8-pin (x1), RJ-45
USB	USB 2.0 type-A 4-pin (x1) for USB Memory

## UHC-8300 Camera Head Supplied Accessories

Operation manual CD-ROM (x1) JP,

Supplied Accessories	GB, CS Cable clamp belt (x1) Camera number label (x1) Screws +B3 (x2) for cable clamp belt Lens mount cap (x1)
----------------------	--

## UHCU-8300 CCU General

Power Requirement	AC 100 to 127V, 200V to 240 V, 50/60 Hz
Consumption Current	AC IN 1: 4.0A (max.) AC IN 2: 6.2A (max.)
Operating Temperature	5°C to +40°C 41°F to +104°F
Storage Temperature	-20°C to +60°C -4°F to +140°F
Dimensions (W x H x D) *1	482 (440) x 221 x 500 mm 19 (17 1/2) x 8 3/4 x 19 3/4 inches
Mass	Approx. 24 kg Approx. 52 lb 15 oz
Video Signal	8K 4320: 119.88p, 100p, 59.94p, 50p (SQD-2SI, 2SI-2SI) 4K 2160: 59.94p, 50p (2SI, SQD, Level-A/B)



HD 1080: 59.94p, 59.94i, 50p, 50i

\*1

The values for dimensions are approximate and excluding the protrusions.

## UHCU-8300 CCU Input/Output

Camera

Optical Fiber (x1)

D-sub 50-pin, female (x1)

Intercom/Program/Tally

- INTERCOM (PROD/ENG), 4Wire/RTS/Clear-Com, 0 dBu
- PGM 2 systems, -20/0/+4 dBu
- TALLY (R, G, Y)
- FLAG

RCP/CNU

8-pin multi connector, female (x1)

Trunk

12-pin, female (x1)  
RS-232C or RS-422A, 1 system

LAN

8-pin (x1), RJ-45

Network Trunk

8-pin (x1), RJ-45

Focus Demand	20-pin, female (x1)
MAG Control	14-pin, female (x1)
NMI-LAN (Option: TBD)	QFSP+ (x2), 40G Base-SR (by transceiver module)
USB	USB 2.0 type-A 4-pin (x1) for USB Memory

## UHCU-8300 CCU Input

AC	AC 100 to 127V, 200V to 240 V (x2)
4K Return	BNC type (x8) 12G-SDI, SMPTE ST2082-10 3G-SDI, SMPTE ST424/425-5, 2 systems
HD Return	BNC type (x4) 3G-SDI, SMPTE ST424/425-1 HD-SDI, SMPTE ST292-1, 4 systems
Reference	BNC type (x2), In: HD: SMPTE ST274, Tri-Level Sync, 0.6 Vp-p, 75 Ω SD: Black Burst (NTSC: 0.286 Vp-p, 75 Ω / PAL: 0.3 Vp-p, 75 Ω) Out: Loop-Through

Prompter	BNC type (x1), In: VBS, 1.0 Vp-p, 75 Ω, 1 system
----------	--

HD Prompter	BNC type (x1) HD-SDI: SMPTE ST292-1
-------------	--

## UHCU-8300 CCU Output

8K (SLOT-1)	BNC type (x16) 12G-SDI: SMPTE ST2082-10/12, 2 systems for 59.94p/50p, 1 system for 119.88p/100p 3G-SDI: SMPTE ST424/425-1, 1 system
-------------	---

4K MAG (SLOT-2)	BNC type (x4) 12G-SDI: SMPTE ST2082-10 3G-SDI: SMPTE ST424/425-5
-----------------	--

4K (SLOT-3)	BNC type (x8) 12G-SDI: SMPTE ST2082-10 3G-SDI: SMPTE ST424/425-5, 2 systems
-------------	---

4K Monitor (SLOT-4)	BNC type (x4) 12G-SDI: SMPTE ST2082-10 3G-SDI: SMPTE ST424/425-5
---------------------	--

HD (SLOT-5)	BNC type (x4) 3G-SDI: SMPTE ST424/425-1 HD-SDI: SMPTE ST292-1
-------------	---

	3G-SDI/HD-SDI, character signal selectable
Sync	BNC type (x1) HD SYNC: SMPTE ST274, tri-level sync, 0.6 Vp-p, 75 Ω SD SYNC: composite sync, 0.3 Vp-p, 75 Ω HD SYNC/SD SYNC selectable
Audio CH-1, CH-2	XLR 3-pin, male (x2), 0/-20/+4 dBu

## UHCU-8300 CCU Supplied Accessories

Supplied Accessories	Tally number plate (x1 set) Operation manual CD-ROM (x1), JP, GB, CS
----------------------	---

## UKCU-IP01F Option Interface General

Power Requirement	DC 12V
Power consumption (Max.)	70 W
Operating Temperature	5°C to +40°C 41°F to +104°F
Storage Temperature	-20°C to +60°C -4°F to +140°F

Dimensions (W x H x D) *1	340 x 21 x 239 mm 13 1/2 x 5/6 x 9 1/2 inches
------------------------------	--

Mass	Approx. 0.8 kg Approx. 1 lb 12 oz
------	--------------------------------------

*1	The values for dimensions are approximate and excluding the protrusions.
----	--

### UKCU-IP01F Option Interface Output

Output *2	QSFP+, conforms to 40GBASE-SR/LR
-----------	----------------------------------

*2	Transceivers, QSFP+, are not included.
----	--

### UKCU-IP01F Option Interface Supplied Accessories

Supplied Accessories	Operation manual (x1), JP, GB, CS
----------------------	-----------------------------------

### UKCU-8001 Optional Interface General

Power Requirement	DC 12V
-------------------	--------

Power consumption (Max.)	110 W
-----------------------------	-------

Operating Temperature	5°C to +40°C 41°F to +104°F
Storage Temperature	-20°C to +60°C -4°F to +140°F
Dimensions (W x H x D) *1	340 x 41 x 251 mm 13 1/2 x 1 5/8 x 10 inches
Mass	Approx. 1.5kg Approx. 3 lb 4.9 oz
*1	The values for dimensions are approximate and excluding the protrusions.

## UKCU-8001 Optional Interface Output

Output *2	QSFP28, conforms to 100GBASE-SR4
*2	Transceivers, QSFP28, are not included.

## UKCU-8001 Optional Interface Supplied Accessories

Supplied Accessories	Operation manual (x1), JP, GB, CS
----------------------	-----------------------------------

## UZCU-SNMP80 Optional Software General

UZCU-SNMP80

SNMP Agent Software

Related products



### **HDRC-4000**

HDR Production Converter Unit



### **RCP-3500**

Remote-control panel for HDC/HSC/HXC series cameras



### **RCP-3501**

Remote-control panel for HDC/HSC/HXC series cameras



### **MSU-3000**

Master setup unit, multi camera remote control panel for system cameras (horizontal type)



### **MSU-3500**

Master setup unit, multi camera remote control panel for system cameras (vertical type)



### **HDVF-L750**

Full HD 7-inch LCD viewfinder



### **HDVF-L770**

Full HD 7-inch LCD viewfinder, adjustable with large handle



### **RCP-1500**

Joystick type of Remote Control Panel for HDC/HSC/HXC series cameras. 4 units in 19-inch EIA rack.



### **RCP-1501**

Dial type of Remote Control Panel for HDC/HSC/HXC series cameras. 4 units in 19-inch EIA rack.



### **MSU-1000**

Master setup unit, multi camera remote control panel for HDC / HSC cameras (horizontal type)



### **MSU-1500**

Master setup unit, multi camera remote control panel for HDC / HSC cameras (vertical type)



### **VCT-14**

TRIPOD ADAPTOR FOR PORT. CAMERAS/CAMC.

## Gallery



NETWORKED **LIVE**





