

## UNI-OTBC2

Temperature-controlled vandal resistant outdoor security camera housing



### Overview

This vandal-resistant housing is compatible with Sony SNC-EB6xx and SNC-VB6xx series box-type security cameras.

Suitable for wall or pole mounting outdoors, the UNI-OTBC2 meets NEMA Type 4 and IP66 standards for resistance to dust/moisture penetration. It's also IK10 impact rated.

Ideal for use in a wide range of climatic environments, the camera housing features an adjustable sunshield plus a thermostatically controlled heater and fan cooling system.

Operating voltage 24V AC or 12V DC.

### Related products



#### **SNC-EB600**

Box-type 720p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



#### **SNC-EB600B**

Basic Box-type 720p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



#### **SNC-EB630**

Box-type 1080p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



#### **SNC-EB630B**

Basic Box-type 1080p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



## **SNC- EB640**

Box-type Full HD IP  
Network Camera (E-  
Series)



## **SNC- VB600**

Box-type 720p/60 fps  
Camera Powered by  
IPELA ENGINE EX™ - V  
Series



## **SNC- VB600L**

Box-type 720p/60 fps  
Camera Powered by  
IPELA ENGINE EX™ - V  
Series



## **SNC- VB630**

Box-type 1080p/60 fps  
Camera Powered by  
IPELA ENGINE EX™ - V  
Series



## **SNC- VB635**

Box-type 1080p/60 fps  
Camera with Half-inch  
Exmor™ CMOS Sensor  
Powered by IPELA  
ENGINE EX™ - V Series



## **SNC- VB640**

Box-type Full HD  
1080p/60fps IP  
Network Camera (V-  
Series)

## Gallery

