

# UNI-OPL7C3

Outdoor Pressurized dome camera housing



## Overview

Applicable Camera Models;  
 - SNC-RX550P - SNC-RX530P - SNC-RX570P Fixing Method;  
 -SNCA-WM20G (wall) -SNCA-CEILING (ceiling) -SNCA-WM20FC (see note) Rating;  
 -IP67 Operating Temperature;  
 --29°C to +50°C (SNCA-HEATER) Voltage;  
 -24 volts AC Optional accessories;  
 -SNCA-CLEAR/2 (included)  
 -SNCA-TINTED/2

## Related products



### SNC-ZR550

720p/30 fps Rapid Dome camera capable of transmitting both analogue video and HD IP images over your existing analogue coax infrastructure



### SNC-RH124

720p/30 fps Rapid Dome Camera



### SNC-EB600B

Basic Box-type 720p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



### SNC-ZP550

720p/30 fps PTZ camera capable of transmitting both analogue video and HD IP images over your existing analogue coax infrastructure



### SNT-RS1U

Video Network Station rack mount for the SNT-EP154 and SNT-EX154



### SNC-ZB550

Box-type 720p/30 fps camera capable of transmitting both analog video and HD IP images over your existing analog coax infrastructure



### SNC-CH140

Box-type 720p/30 fps Camera - V Series



### SNC-ER521

Standard Definition (PAL) Rapid Dome Network Camera



### SNC-EP521

Standard Definition (PAL) PTZ Network Camera



### SNC-CH120

Box-type 720p/30 fps Camera - E Series



### SNC-CH220

Box-type 1080p/30 fps Camera - E Series



### SNC-VB600B

Box-type 720p/30 fps Camera Powered by IPELA ENGINE EX™ - V Series



### SNC-ER580

1080p/30 fps Rapid Dome Camera - E Series



### SNC-EB630

Box-type 1080p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



### SNC-VB600

Box-type 720p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



### SNC-EP580

1080p/30 fps PTZ Camera - E Series



### SNC-EB600

Box-type 720p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



### SNC-ER550

720p/30 fps Rapid Dome Camera - E Series



### SNC-EB630B

Basic Box-type 1080p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series

## Gallery

