

ECM-678

Shotgun Electret condenser microphone



Overview

For superior sound quality, choose the ECM-678. It delivers superior sensitivity of -28 dB (0dB=1V/Pa) and extremely low inherent noise of less than 16 dB SPL. This microphone balances the need for a compact size with its ability to deliver excellent performance. The result is a highly directional microphone that is only 250 mm in length.

Specifications

Audio Section

| | |
|---------------------------|----------------------------------|
| Capsule Type | Mono Electret Condenser |
| Frequency Response | 40 Hz to 20 kHz |
| Directivity | Uni-directional (super-cardioid) |
| Sensitivity *[1] | -28 dB +/-3 dB |
| Output Impedance * [2] | 200Ω ±20%, Balanced |
| Dynamic Range | 111 dB or more |

| | |
|---|------------------------------------|
| Signal-to-Noise Ratio *[3] | 78 dB or more |
| Inherent Noise *[4] | 16 dB SPL or less |
| Induction Noise From External Magnetic Field *[5] | 0 dB SPL or less |
| Wind Noise *[6] | 60 dB SPL or less (without screen) |
| Maximum Input Sound Pressure Level *[7] | 127 dB SPL |

General Section

| | |
|--------------------|---|
| Connector | XLR-3-12C (male) |
| Mic Cable | XLR-3 to XLR-3 480 mm 18.9 inches |
| Power Requirements | External, DC 48 V +/-4 V |
| Dimensions *[8] | ϕ 20 x 250 mm ϕ 13/16 x 9 7/8 inches |
| Mass | Approx. 7 oz Approx. 200 g |
| | Windscreen (1) |

| | |
|----------------------|--|
| Supplied Accessories | Stand adaptor (2) Short LR cable (for camcorder use) (1) Operating instructions (1) Mic spacer (2) Mic holder (1) Carrying case (1) |
|----------------------|--|

Notes

| | |
|------|---|
| Note | <ul style="list-style-type: none">*[1] 0 dB = 1 V/Pa, at 1 kHz*[2] Output impedance at 1 kHz*[3] A-weighted, 1 kHz, 1 Pa.*[4] 0 dB SPL = 20 μPa.*[5] dB SPL/1E-7 T, 0 dB SPL = 20 μPa.*[6] Wind noise at 2m/s (0 dB SPL = 20 μPa.)*[7] 0 dB SPL = 20 μPa.*[8] The values for dimensions are approximate. |
|------|---|

Related products



HXC-FB80

Three 2/3-inch
Exmor™ CMOS sensor
HD colour studio

camera

Gallery

