

## HDVF-C35W



### Specifications

#### General

|              |  |
|--------------|--|
| Power supply | 10.5 to 17.0 V DC (supplied by the camera) |
|--------------|--|

|                   |  |
|-------------------|--|
| Power consumption |  |
|-------------------|--|

|                       |                                     |
|-----------------------|-------------------------------------|
| Operating temperature | -20 °C to +45 °C (-4 °F to +113 °F) |
|-----------------------|-------------------------------------|

|                     |                                     |
|---------------------|-------------------------------------|
| Storage temperature | -20 °C to +60 °C (-4 °F to +140 °F) |
|---------------------|-------------------------------------|

|      |  |
|------|--|
| Mass |  |
|------|--|

#### Performance

|            |  |
|------------|--|
| Brightness |  |
|------------|--|

|            |                   |
|------------|-------------------|
| Resolution | 500 or more lines |
|------------|-------------------|

|                   |  |
|-------------------|--|
| Supported formats |  |
|-------------------|--|

|                    |  |
|--------------------|--|
| Colour temperature |  |
|--------------------|--|

---

Indicators

---

Y

---

Connector

Camera connector      Round type 20-pin

---

Supplied Accessories

Operation manual (1)

---

## Gallery

