

## HDVF-L750

Full HD 7-inch LCD viewfinder



### Overview

#### **Large Full HD 1920 x 1080 7-inch LCD panel ideal for 4K live production in operation with Sony studio cameras, XDCAM camcorders, F65 and PMW-F55**

The HDVF-L750 Full HD 7-inch LCD viewfinder is usable with the whole range of Sony studio cameras, XDCAM camcorders (with supplied VF cable and V-shoe adaptor), F65 and PMW series camcorders such as the PMW-F55 and PMW-F5 in 4K and HD live production configurations. The 1920 x 1080 LCD panel allows for more precise focusing, with a very high 1000:1 contrast ratio and WFM (waveform monitor) function for very precise exposure control. A 3G-SDI input connector adds flexibility for viewing external sources apart from the camera signal, while two assignable switches on the bezel allow for bespoke setups. The viewfinder also has a simple hood to help minimise glare.

#### **Full HD 1920 x 1080 7-inch LCD panel ideal for 4K and HD live production**

Easier and more precise focusing, especially in 4K applications in operation with F65 and PMW-F55 cameras.

#### **1000: 1 high contrast ratio**

Better picture viewing in outside broadcast live applications.

#### **WFM (waveform monitor) function**

## Features

All-in-one picture control monitoring for very precise exposure control.

### **External 3G-SDI input connector**

Allows you to check external video sources in the field, including third party equipment.

### **Full HD 1920 x 1080 7-inch LCD panel with high contrast ratio**

The precision 1920 x 1080 pixels LCD panel delivers stunning Full HD quality for easier and more precise focusing, especially in 4K applications in operation with F65 and PMW-F55 cameras. The viewfinder also attaches to all Sony studio cameras and XDCAM camcorders (with supplied VF cable and V-shoe adaptor).

### **High contrast ratio**

The very high 1000:1 contrast ratio provides better picture viewing in outside broadcast live applications.

### **WFM (waveform monitor) function**

The WFM function provides all-in-one picture control monitoring for very precise exposure control and optimal focus adjustment.

### **External 3G-SDI input connector**

The 3G-SDI input allows you to monitor SDI external signals up to 3G-SDI. You can check external video sources in the field, including third party equipment, and have an additional video return in addition to the camera.

### **Assignable switches on bezel**

The HDVF-L750 offers two assignable switches on the bezel for bespoke setups.

### **Simple hood, plus HDVF cable**

The viewfinder is supplied with a simple hood, as well as a HDVF cable.

## Related products



### **HXC-FB80**

Three 2/3-inch Exmor™ CMOS sensor HD colour studio camera



### **UHC-8300**

UHC-8300 8K 3CMOS sensor Camera system includes UHCU-8300 8K Camera Control Unit, UKCU-8001 (8K ST 2110 Interface), UZCU-SNMP80 (SNMP for 8K ST 2110), UKCU-IP01F (Networked Media Interface)



### **HDLA-3501**

Large Lens Adaptor



### **HDLA-3505**

Large Lens Adaptor



### **HDC-3200**

2/3-inch 4K 3CMOS Camera System

## Gallery

