

## LKRL-Z214

1.35x - 2.40x Zoom Lens for the SRX-R320P



### Overview

#### 1.35x - 2.40x Zoom Lens for SRX-R320P

Optional zoom lens for use with the SXR4 4K R320 projector 1.35x to 2.40x zoom lens with memory feedback. This lens uses a feedback circuit that reports focus and zoom position to the projector. This allows the operator to preset and recall different lens settings from the projector function memories. This offers instant and automated screen sizing for video formats using different aspect ratios.

### Specifications

#### General

f-stop number	f/2.8
Operating temperature	0°C to +40°C
Storage temperature	-20°C to +60°C
Operating humidity	0% to 90% (without condensation)
Storage humidity	0% to 90% (without condensation)

---

Dimensions(W/H/L)	Approx. 187mm x 222mm x 455mm (7 3/8 x 8 3/4 x 17 7/8 inches)
-------------------	---

---

Mass.	Approx. 11.0kg (24 lb 3 oz)
-------	-----------------------------

---

## Gallery

