

PSS-650P

Projector Ceiling Bracket for Installation



Overview

Projector Ceiling Bracket for Installation

Specifications

Adjustable range

Up/down position	1,000~1,675 mm / 39 3/8~65 15/16 inches 650~975 mm / 25 19/32~38 3/8 inches (cut) 1,700~2,975 mm / 66 15/16~117 1/8 inches (x 2 units) (25mm pitch adjustment)
------------------	--

Dimensions (W x H x D)

Dimensions (W x H x D)	51 x 695 x 58.5 mm / 2 x 27 3/8 x 2 5/16 inches
------------------------	---

Dimensions (W x H x D) *without protrusions (Adjustment knob)

Dimensions (W x H x D) *without protrusions (Adjustment knob)	51 x 695 x 58.5 mm / 2 x 27 3/8 x 2 5/16 inches
---	---

Mass

Mass	Approx. 2.2 kg / 4.8 lb
------	-------------------------

Maximum load

Maximum load	30 kg / 66 lb
--------------	---------------

Note

Note	Max: up to 2 units connection
------	-------------------------------

Color

Color	Black
-------	-------

Gallery



© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.