

# SXS-1 Series Memory Card

32GB, 64GB, and 128GB SxS-1 Series Memory Card



## Overview

**Rugged, proven technology to support all the recording features of the XDCAM EX camera lineup**

**32GB, 64GB, and 128GB capacity**

**Read speed up to 440MB/s**

**Supports EB Streaming between card and Sony camcorders enabling constant 2 way communication and insuring stable recording while avoiding speed degradation.**

**Enhanced media management with Memory Media Utility**

Memory Media Utility dedicated PC software for Sony memory media products (available from download) provides enhanced media management.

**10 year warranty**

**Important Notice**

If you use SBS-64G1C or 128G1C with compatible devices listed below, you need to update the device's system software to the version shown in parentheses or higher. For details, see the information on each device's website.

Compatible devices requiring the system software update (version number):

- PXW-X160 (V4.0)
- PXW-X180 (V4.0)
- PXW-X400 (V2.0)
- PXW-X500 (V4.0)
- PMW-F5 (V8.0)
- PMW-F55 (V8.0)
- PDW-HD1550 (V1.34)
- PMW-1000(V1.43)
- XDS-1000 (V3.21)
- XDS-PD1000 (V3.21)
- XDS-PD2000 (V3.21)

## Specifications

General	
Interface	ExpressCard/34, PCI Express Gen2
Read speed	3.5Gbps (=440MB/s)*

Write Speed	1.6Gbps (=200MB/s)* : SBS-64G1C, SBS-128G1C 110MB/s* : SBS-32G1C
Capacity	32GB** : SBS-32G1C 64GB** : SBS-64G1C 128GB** : SBS-128G1C
Model Name	SBS-32G1C, SBS-64G1C, SBS-128G1C
Operating Temperature	-25°C-65°C
Storage Temperature	-40°C-85°C
Weight	Approx.27g
Dimension (W x H x D)	Approx.34 x 5 x 75 mm (excluding the projecting parts)

Reliability****	
Shock Resistance	1,500G
Vibration Proof	15G
Insertion/Removable Durability	30,000times
Shock Absorption	150cm

Notes	
Note	<p>* Based on Sony internal testing, actual speed varies upon the measurement conditions.</p> <p>** Under condition that product is operating with PCIe Gen1 interface.</p> <p>***1GB= 1 billion bytes. A portion of the memory is used for system files and may vary.</p> <p>****Performance test by Sony internal Standard</p>

Related products



**SBAC-T40**

SxS memory card Thunderbolt 3 reader/writer

Gallery

