

BVM-HX3110

30.5-inch 4K TRIMASTER HX™
Professional Master Monitor



NETWORKED LIVE 4K SR Live HDR

Specifications

Picture Performance

| | |
|-----------------------------------|---|
| Panel | α -Si TFT Active Matrix LCD |
| Picture size (diagonal) | 30.5 inches (775.2 mm) |
| Effective Picture size (H x V) | 685.7 x 361.6 mm (27 x 14 1/4 inches) |
| Resolution (H x V) | 4096 x 2160 pixels |
| Aspect | 1.90 : 1(17:9) |
| Pixel efficiency | 99,99% |
| Display colors | 1.07 billion |
| Panel frame rate | 96 Hz / 100 Hz / 120 Hz (96 Hz and 120 Hz are also compatible with 1/1.001 frame rates) |
| Viewing angle (panel) | 89°/89°/89°/89° (up/down/left/right contrast > |

| | |
|---------------------------|---|
| specification) | 10:1) |
| Normal scan | 0% scan |
| Underscan | 3% underscan |
| Color temperature | D50, D60, D65, D93, DCI*1, and user 1–10 (5,000 K to 10,000 K adjustable), DCI XYZ |
| Luminance | 4,000 cd/m ² (typical)*2 1,000 cd/m ² (typical)*3 |
| Color space (Color gamut) | ITU-R BT.2020*4, ITU-R BT.709, EBU, SMPTE-C, DCI-P3*4, S-Gamut3*4, S-Gamut3.Cine*4 |
| Transmission Matrix | ITU-R BT.2020 (Non-constant luminance is supported), ITU-R BT.709 |
| EOTF | 2.2, 2.4, 2.6, CRT, 2.4 (HDR), S-Log3, S-Log3 (Live HDR), SMPTE ST 2084, ITU-BT.2100 (HLG) |
| Warm-up time | Approx. 30 minutes To provide stable picture quality, turn on the power of the monitor and leave it in this state for more than 30 minutes. |

Input

| | |
|-----|--|
| SDI | (12G/6G/3G/HD-SDI) BNC (x2), (3G/HD-SDI) BNC (x2), Input impedance: 75 Ω unbalanced |
|-----|--|

| | |
|------------|-------------------------|
| HDMI Input | HDMI (HDCP2.3/1.4) (x1) |
|------------|-------------------------|

| | |
|-----------|---------------------|
| IP(LAN)*5 | SFP28(x2), 25G BASE |
|-----------|---------------------|

| | |
|-----------------|--|
| Parallel Remote | RJ-45 8-pin (x1) (Fixed pin assignment) |
|-----------------|--|

| | |
|---------------------|---|
| Serial Remote (LAN) | Ethernet, 10BASE-T/100BASE-TX RJ-45 (x1) |
|---------------------|---|

| | |
|-----------|-----------------------------|
| USB input | USB (USB2.0) connector (x1) |
|-----------|-----------------------------|

Output

| | |
|------------------------------|---|
| Enhanced Monitor Output*6 | (12G/6G/3G/HD-SDI) BNC (x1), Output impedance: 75 Ω unbalanced |
|------------------------------|---|

| | |
|------------|---|
| SDI Output | (12G/6G/3G/HD-SDI) BNC (x2), (3G/HD-SDI) BNC (x2), Output impedance: 75 Ω unbalanced |
|------------|---|

| | |
|----------------------|-----------------------|
| Audio Monitor Output | Stereo mini jack (x1) |
|----------------------|-----------------------|

| | |
|------------------|-----------------------|
| Headphone Output | Stereo mini jack (x1) |
|------------------|-----------------------|

General

| | |
|--|--|
| Power requirement | AC 100 V to 240 V, 6.6 A to 2.5 A, 50/60 Hz |
| Power consumption | Approx. 610 W (max.) 0.3 W In off-mode (When the Power switch is off) |
| Off Mode Activated | After About 60 Minutes |
| Operating temperature | 0°C to 35°C (32°F to 95°F) Recommended: 20°C to 30°C (68°F to 86°F) |
| Operating humidity | 30% to 80% (no condensation) |
| Storage / transport temperature | -20°C to +60°C (-4°F to +140°F) |
| Storage / transport humidity | 10% to 80% |
| Operating / storage / transport pressure | 700 hPa to 1060 hPa |
| Dimensions (W x H x D) | 778 x 519 x 230 mm (30 3/4 x 20 1/2 x 9 1/8 inches) |
| Mass Approx. | 29 Kg (63 lb 15 oz) |
| Supplied accessories | AC power cord (1)AC plug holder (1)Before Using This Unit (1) |

Notes

| | |
|----|---|
| *1 | DCI: x=0.314, y=0.351 |
| *2 | This luminance value is a typical value at D65 (x, y = 0.3127, 0.329) with a 10% white window. This value is not guaranteed. To avoid irreversible panel damage, an auto brightness limiter is enabled if the total amount of current or screen temperature exceeds the maximum capacity of the BVM-HX3110. |
| *3 | Panel specification (all white signal). This luminance value is typical at D65 (x, y = 0.3127, 0.329) and is not guaranteed. |
| *4 | The BVM-HX3110 does not cover selected color space in full. |
| *5 | Sony OTM-25GSR and OTM-25GLR transceivers, and modules with power consumption of 1.0 W or lower are supported. Copper DAC (Direct Attach Cable) is not supported. |

*6

Either BVML-H10, BVML-S10 or BVML-T10 optional license is required.

Related products



FWD-55A95L

55" Sony BRAVIA OLED 4K HDR Display with Google TV, including 3 years PrimeSupport



BVML-F10

Fast response license for for BVM-HX3110/ HX1710/ HX1710N



BVML-SN10

SNMP license for for BVM-HX3110/HX1710N



BVML-T10

3D LUT output license for BVM-HX3110/HX1710/HX1710N



BVML-S10

Signal conversion output license with a 3D LUT feature for BVM-HX3110/ HX1710/ HX1710N



BVML-H10

HDR-SDR conversion license for BVM-HX3110/ HX1710/ HX1710N



BVML-JD10

JPEG XS decoder license for for BVM-HX3110/HX1710N

Gallery

