

## ODBK-103

\*Please contact your local sales representative for details.



### Overview

#### **Extension kit for the ODS-L30M**

#### **A world of solutions**

You'll find Optical Disc Archive solutions from Sony at work in a wide range of environments where speedy, reliable access to your precious data is crucial – along with effortless scalability and attractive ownership costs. Optical Disc Archive provides archiving solutions across seven key industries, from digital Media Asset Management to healthcare, banking, education and more.

See our ODA solutions page or contact us now to see how ODA solutions can boost the profitability of everyone's business.

### Related products



#### **ODS-L30M**

\*Please contact your local sales representative for details.



#### **ODS-L60E**

\*Please contact your local sales representative for details.



#### **ODS-L100E**

\*Please contact your local sales representative for details.



#### **ODS-D280F**

Optical Disc Archive fibre channel drive unit for the ODS-L30M/L60E/L100E PetaSite scalable library with very high transfer speeds of 1Gbps write (verify on) and 2Gbps read

using ODC-3300R  
Generation 2 cartridge



## **ODS-D77F**

Optical Disc Archive  
fibre channel drive  
unit for ODS-L30M  
PetaSite scalable  
library with transfer  
speeds up to 1,150  
Mbps (read) and 780  
Mbps (write-once  
disc) or 310 Mbps  
(rewritable disc)



## **ODS- D380F**

\*Please contact your  
local sales  
representative for  
details.

## Gallery

