

# HDTX-100

HD triax adaptor for HDC-1500/1000 cameras



## Overview

The HDTX100 and HAFX100 HD Triax Adaptors extensively expand applications of the HDC1000/HDC1500. By converting optical fiber transmission to the widely used triax transmission system, they enable high-quality pictures to be transmitted from the HDC1000 or HDC1500 camera or HDC1500 mounted on the HDLA1500 over long distances - up to 1400 m (4500 feet) with a 14.5 mm dia. triax cable or 1000 m (3200 feet) with a 13.2 mm dia. triax cable. \* Converts optical fiber transmission to the widely used triax transmission system \* Long distance transmission - up to 1400 m (4500 feet) with a 14.5 mm dia. triax cable or 1000 m (3200 feet) with a 13.2 mm dia. triax cable.

## Gallery



---

© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.

Export PDF : October 12 2026