

## PSS-650P

Projector Ceiling Bracket for Installation



Overview

### Projector Ceiling Bracket for Installation

Specifications

#### Adjustable range

	1,000~1,675 mm / 39 3/8~65 15/16 inches
Up/down position	650~975 mm / 25 19/32~38 3/8 inches (cut )
	1,700~2,975 mm / 66 15/16~117 1/8 inches (x 2 units) (25mm pitch adjustment)

#### Dimensions (W x H x D)

Dimensions (W x H x D)	51 x 695 x 58.5 mm / 2 x 27 3/8 x 2 5/16 inches
------------------------	---

Dimensions (W x H x D) \*without protrusions (Adjustment knob)

Dimensions (W x H x D)  
\*without protrusions  
(Adjustment knob)      51 x 695 x 58.5 mm / 2 x 27 3/8 x 2  
5/16 inches

---

## Mass

Mass      Approx. 2.2 kg / 4.8 lb

---

## Maximum load

Maximum load      30 kg / 66 lb

---

## Note

Note      Max: up to 2 units connection

---

## Color

Color      Black

---

## Gallery

