

## DWT-B03R

DWX Series digital wireless  
microphone bodypack  
transmitter



### Overview

#### **Superb audio quality and stable operation in a wide range of environments**

The third generation of Sony's acclaimed DWX series, this high performance digital wireless bodypack transmitter is an ideal choice for live sound applications including theatre and concerts, as well as studio based TV production and ENG/EFP.

Light and compact (27% smaller than its DWT-B01N predecessor), the DWT-B03R features a tough magnesium body that's resistant to rain, spray and sweat.

Sony's advanced digital audio processing, encryption and RF transmission technologies assure secure, stable transmission and reception of very high quality audio with low latency.

The DWT-B03R is ideal for use in large-scale multi-channel productions, supporting up to 21 simultaneous channels per 8MHz TV band or up to 16 simultaneous channels per 6MHz TV band.

The DWT-B03R is compatible with Sony Wireless Studio control software for PC (Ver 5.0 or later) , allowing flexible remote operation. Remote control of up to 82 transmitters is possible using the Cross Remote™ function combined with the RMU-01

remote control unit (available separately).

## Features

### **Small, lightweight and robust magnesium body**

27% smaller than its DWT-B01N predecessor

### **Very high quality wireless audio**

Advanced Sony codec design assures superb audio quality, with a high dynamic range of more than 106 dB, plus a wide frequency response of 20 Hz - 22 kHz and excellent transient response.

### **Low-latency audio**

Advanced Sony codec design reduces audio latency to as little as 1.2msec\*

\*DWT-B03R and DWR-R03D total delay with codec mode2 and analog output

### **Rain, sweat and spray proof\***

Ideal for musical, film production or outdoor operation, the DWT-B03R features a tough magnesium body with a moisture-resistant housing gasket and splash-proof connector that resists rain, sweat and spray.

\*IPX4/IPX5 rating based on standard testing by Sony.

### **Long battery life**

Perform for longer with the high-capacity rechargeable NP-BX1 Li-ion battery (approx. 7 hours). The DWT-B03R is compatible with the optional BC-DWX1 Dual Charger.

### **148MHz\* wideband**

Contributes to the reduction of equipment and burden of maintenance.

\*depends on version

## **High density multi-channel operation**

Ideal for large-scale productions, the DWT-B03R supports high-density simultaneous multi-channel operation: 375kHz spacing accommodates up to 21 channels per 8MHz TV band or up to 16 simultaneous channels per 6MHz TV band.

## **AES 256bit encryption**

For secure encrypted transmission

## **Easy, versatile remote control**

The DWT-B03R is compatible with Sony's Wireless Studio control software for PC (Version 5.0 or later). Up to 82 transmitters can be controlled using the Cross Remote™ function and RMU-01 remote control unit (available separately).

## **Selectable RF output power**

RF output power level is selectable (2mW/10mW/25mW) to prioritise stable multi-channel or long distance operation.

## **OLED display**

The easy-to-read OLED display gives confirmation of channel number, RF signal status, user name, user group and lock status.

## **Phase reverse mode**

It can change the audio phase by the menu.

## **User setting memory**

Settings can be easily stored to the memory of DWT-B03R.

## **Setting lock**

Transmitter settings can be locked to prevent accidental operation during performance.

## **Transmitter/receiver identifying function**

Paired transmitters/receivers are identified by blinking display.

## **Small 3-pin connector with lock**

## Specifications

### Specifications

Wireless Interface	WiDIF-HP
Oscillator Type	Crystal-controlled PLL Synthesizer
Antenna Type	$\lambda/4$ flexible wire
Type of Emission	G1E or G1D
Carrier Frequencies - UC7	470.125 MHz to 607.875 MHz, 614.125 MHz to 615.875 MHz, 25 kHz steps
Carrier Frequencies - CE7	L: 470.025 MHz to 614.000 MHz, 25 kHz steps H: 566.025 MHz to 714.000 MHz, 25 kHz steps
Carrier Frequencies - J	L: 470.150 MHz to 614.000 MHz, 25 kHz steps MH: 566.025 MHz to 713.850 MHz, 25 kHz steps G: 1240.150 MHz to 1251.825 MHz, 1253.175 MHz to 1259.850 MHz, 25 kHz steps B: 806.125 MHz to 809.750 MHz, 125 kHz steps
RF Power	2 mW/10 mW/25 mW (e.r.p) selectable

Input Connector	Small 3-pin connector with lock
Reference Input Level	MIC: -60 dBV (-58 dBu), 1 kHz (at 0-dB attenuator level) / LINE: +4 dBu, 1 kHz
Maximum Input Level	MIC: -22 dBu (with 0 dB attenuator), LINE: +24 dBu
Audio Attenuator Adjustment Range	0 to 48 dB (3 dB steps, MIC input mode only)
Frequency Response	Transmission: 20Hz to 22kHz (typical)
Dynamic Range	106 dB typical (A-weighted, T.H.D=1%)
Distortion (T.H.D)	MODE1, MODE2: 0.03% or less, MODE3: 0.3% or less
Audio Delay*	MODE1: 0.8 msec (total: 2.7msec) /MODE2: 0.7 msec (total: 1.2msec)/MODE3: 1.8 msec (total 3.7msec) *Analog output
Wireless Remote Control	Cross Remote (2.4-GHz IEEE802.15.4 compliant)
Display	OLED

Power Requirements	DC 3.6 V (with Rechargeable Battery Pack: NP-BX1)
Battery Operating Time	Approx. 7 hours with Sony's NP-BX1 at 25°C(77°F) at 10-mW output (with the wireless remote control function off and DIMMER MODE set to AUTO OFF)
Operating Temperature	0°C to 50°C / 32°F to 122°F
Storage/Transport Temperature	-20°C to +60°C / -4°F to +140°F
Dimensions (W x H x D)	Approx. 53 x 60 x 17 mm (60 x 60 x 17 mm with the projection parts) (excluding the antennas)
Mass	Approx. 99 g
Supplied Accessories	Belt Clip (1) Carrying case (1) NP-BX1 (1) Scribble sheet (1) CD-ROM (1)

## Notes

This product is available in a

## Important note

variety of different frequency range models to suit the regulatory requirements of individual countries. Please contact your Sony reseller for more information on which product will best suit your specific needs.

---

## Related products



### **ECM-77LM**

Miniature omni-directional electret condenser microphone



### **BC-DWX1**

Dual battery charger for DWT-B03R wireless transmitter



### **DWR-R03D**

DWX Series 2-channel digital wireless receiver



### **ECM-90LM**

Electret condenser microphone



### **DWR-S03D**

DWX Gen3 2-channel digital wireless slot-in receiver

## Gallery

