

SCA-M30

High quality, ceiling microphone for IP security cameras.



Overview

Microphones are a powerful addition to IP camera surveillance systems, adding an audio layer to the information captured by a security system. They can help draw an operator's attention to incidents or add meaning to an otherwise unintelligible scene. In monitored meetings or interrogations, a ceiling-mounted microphone adds an essential soundtrack to the video recording.

The SCA-M30 is an unobtrusive, indoor microphone which is optimised for capturing clear, high quality sound. Its high sensitivity is enhanced by physical protection against vibration and a filter to reject unwanted low-frequency noise.

Installation is easy, with a range of ceiling mounting options. It connects directly to Sony's IP cameras, which also supply the microphone's operating power.

Features

Highly Sensitive

Capture even the quietest sounds with an extremely sensitive electret transducer.

High Pass Filter to remove low frequency environmental noise

A high pass filter blocks low frequency noise from fans, air conditioning, traffic, etc. improving the clarity of acquired audio.

Housing minimises unwanted noise

Acoustic shielding suppresses noise from the sides and back of the microphone allowing effective pickup from the front.

Simple to set audio pickup direction

Set the direction of maximum pickup by simply rotating the microphone protective grill.

Scalable input sensitivity

The input sensitivity of the microphone is easily adjusted to the optimum level for specific installations.

Easy to install

The microphone is easily installed recessed or projecting from a ceiling using only standard tools.

Robust protective housing

The SCA-M30 is encased in a rubber protective shell which is also spring-mounted to minimise the effects of vibration.

Related products



SNC- VB635

Box-type 1080p/60 fps Camera with Half-inch Exmor™ CMOS Sensor Powered by IPELA ENGINE EX™ - V Series



SNC- VB630

Box-type 1080p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



SNC- VB600

Box-type 720p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



SNC- VM632R

Outdoor IR Ruggedized 1080p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



SNC- VM602R



SNC- VM631



SNC- VM630



SNC- VM601

Outdoor IR
Ruggedized 720p/60
fps Camera Powered
by IPELA ENGINE EX™
- V Series

Vandal-resistant
Minidome 1080p/60
fps Camera Powered
by IPELA ENGINE EX™
- V Series

Minidome 1080p/60
fps Camera Powered
by IPELA ENGINE EX™
- V Series

Vandal-resistant
Minidome 720p/60 fps
Camera Powered by
IPELA ENGINE EX™ - V
Series



SNC- VM600

Minidome 720p/60 fps
Camera Powered by
IPELA ENGINE EX™ - V
Series

Gallery

