

## SXS-1 Series Memory Card

32GB, 64GB, and 128GB SxS-1 Series Memory Card



### Overview

**Rugged, proven technology to support all the recording features of the XDCAM EX camera lineup**

**32GB, 64GB, and 128GB capacity**

**Read speed up to 440MB/s**

**Supports EB Streaming between card and Sony camcorders enabling constant 2 way communication and insuring stable recording while avoiding speed degradation.**

**Enhanced media management with Memory Media Utility**

**10 year warranty**

**Important Notice**

### Specifications

#### General

|             |  |
|-------------|--|
| Interface   | ExpressCard/34, PCI Express Gen2                               |
| Read speed  | 3.5Gbps (=440MB/s)*  |
| Write Speed | 1.6Gbps (=200MB/s)* : SBS-64G1C, SBS-128G1C<br>110MB/s* : SBS- |

32G1C

|                       |  |
|-----------------------|--|
| Capacity              | 32GB <sup>**</sup> : SBS-32G1C 64GB <sup>**</sup> : SBS-64G1C 128GB <sup>**</sup> : SBS-128G1C |
| Model Name            | SBS-32G1C, SBS-64G1C, SBS-128G1C   |
| Operating Temperature | -25°C-65°C   |
| Storage Temperature   | -40°C-85°C   |
| Weight                | Approx.27g   |
| Dimension (W x H x D) | Approx.34 x 5 x 75 mm (excluding the projecting parts)   |

## Reliability<sup>\*\*\*\*</sup>

|                                |             |
|--------------------------------|-------------|
| Shock Resistance               | 1,500G      |
| Vibration Proof                | 15G         |
| Insertion/Removable Durability | 30,000times |
| Shock Absorption               | 150cm       |

## Notes

\* Based on Sony internal testing,

## Note

actual speed varies upon the measurement conditions.

\*\* Under condition that product is operating with PCIe Gen1 interface.

\*\*\*1GB= 1 billion bytes. A portion of the memory is used for system files and may vary.

\*\*\*\*Performance test by Sony internal Standard

---

## Related products



### **SBAC-T40**

SxS memory card  
Thunderbolt 3  
reader/writer

## Gallery

