

XDS-1000

XDCAM Deck / IT Server with two SxS memory slots and 1TB HDD



Overview

The XDS-1000 supports the operation of all SxS cards types, including Memory Stick and SDHC cards, using MEAD adaptors. The Internal 1TB Hard Disk Drive and the 1Gigabit Ethernet connection allow a total of about 32 hours of continuous recording in HD422 50Mbps and multi-user simultaneous access to the AV content.

Hybrid XDCAM workflow

The XDCAM Station is a professional media station with built-in storage and interfaces for SxS memory cards, supporting the super fast XDCAM memory workflow. It features better support for multi-task operation, networking and other IT functions. Adding the XDCAM Station to an XDCAM workflow makes file-based operation much more convenient and efficient.

Features

Supports all XDCAM storage formats

The XDS-1000 supports all XDCAM and XDCAM EX file formats, codecs and metadata, effectively offering complete format transparency. It also supports industry-standard VDCP, ftp and CIFS protocols.

Multi-tasking internal storage operations

The 1 TB Hard Disk Drive (HDD) internal storage is capable of multi-tasking when carrying out certain tasks. This increases interoperability and overall efficiency when working with Network Production systems.

Familiar VTR-like user interface

The layout of controls on the XDS deck follows industry-standard conventions already familiar to most users. This makes it easy to use, configure and integrate into the overall workflow.

Enhances network functionality

The XDS-1000 allows users to access growing volumes of files from non-linear editors without file transfer, offering high-speed file transfer and multiple access via a network. The XDS-1000 offers 4 clients for file transfer and 4 clients for network control.

SD / HD cross-conversion

It supports SD and HD as standard with up-conversion record, and up/down/cross-conversion playback.

Specifications

General

Power Requirements	AC 100 V to 240 V, 50/60 Hz
Power Consumption	170W

General

Operating Temperature	5°C to 40°C 42°F to 104°F
Storage Temperature	-20°C to +60°C -4°F to +140°F
Humidity	20% to 90% (relative humidity)
Mass	15.5 kg 34 lb 2 oz
Dimensions (W x H x D) *1	424 x 132 x 460 mm (excluding protrusions) 16 3/4 x 5 1/4 x 18 1/8 inches (excluding protrusions)
Recording/Playback Format (Video)	MPEG HD422 (CBR, 50 Mbps) MPEG HD: - HQ mode (VBR, maximum bit rate: 35 Mbps), - SP mode *2 (CBR, 25 Mbps), - LP mode *2 (VBR, maximum bit rate: 18 Mbps), MPEG IMX (CBR, 50/40 *2 /30 *2 Mbps) DVCAM (CBR, 25 Mbps)
Recording/Playback Format (Audio)	MPEG HD422: 8 ch/24 bits/48kHz, MPEG HD: 4/2 ch/16bits/48kHz, MPEG IMX: 8 ch/16 bits/48 kHz, or 4 ch/24 bits/48 kHz, DVCAM: 4 ch/16 bits/48 kHz
Recording/Playback Format (Proxy Video)	MPEG-4
Recording/Playback Format (Proxy Audio)	A-law (8 ch/8 bits/8 kHz)
Recording/Playback Time (MPEG HD422)	50 Mbps: Approx. 95 min (PFD50DLA), Approx. 43 min (PFD23A)
Recording/Playback Time (MPEG HD)	35 Mbps, 4-ch audio: More than 145 min (PFD50DLA), More than 65 min (PFD23A) 35 Mbps, 2-ch audio (playback only): More than 150 min (PFD50DLA), More than 68 min (PFD23A) 25 Mbps, 4-ch audio: Approx. 190 min (PFD50DLA), Approx. 85 min (PFD23A) 25 Mbps, 2-ch audio (playback only): Approx. 200 min (PFD50DLA), Approx. 90 min (PFD23A) 18 Mbps, 4-ch audio (playback only): More than 248 min (PFD50DLA), More than 112 min (PFD23A) 18 Mbps, 2-ch audio (playback only): More than 265 min (PFD50DLA), More than 122 min (PFD23A)

General

Recording/Playback Time (MPEG IMX)	50 Mbps: Approx. 100 min (PFD50DLA), Approx. 45 min (PFD23A) 40 Mbps: Approx. 120 min (PFD50DLA), Approx. 55 min (PFD23A) 30 Mbps: Approx. 150 min (PFD50DLA), Approx. 68 min (PFD23A)
Recording/Playback Time (DVCAM)	25 Mbps: Approx. 185 min (PFD50DLA), Approx. 85 min (PFD23A)
Search Speed Range (Shuttle Mode)	-20 times to +20 times normal speed
Search Speed Range (Variable Mode)	-2 times to +2 times normal speed
Search Speed Range (Jog Mode)	-1 time to +1 time normal speed
Search Speed Range (Fast Forward/Reverse)	-35/+35 times normal speed

Media Drive

Media Type	SxS Memory Card Drive, ExpressCard/34 (x2)
------------	--

Internal Storage

Storage Type	HDD, SATA, 500 GB, (x3)
Total Capacity (For Recording)	1 TB
Raid	Raid-4
Recording/Playback Time (Internal Storage)	MPEG HD422: 50Mbps: Approx. 30 hour MPEG HD: - 35 Mbps, 4-ch audio: More than 48 hour - 35 Mbps, 2-ch audio: More than 50 hour *2 - 25 Mbps, 4-ch audio: Approx. 63 hour *2 - 25 Mbps, 2-ch audio: Approx. 66 hour *2 - 18 Mbps, 4-ch audio: More than 82 hour *2 - 18 Mbps, 2-ch audio: More than 88 hour *2 MPEG IMX: - 50 Mbps: Approx. 33 hour - 40 Mbps: Approx. 40 hour *2 - 30 Mbps: Approx. 50 hour *2 DVCAM: - 25 Mbps: Approx. 61 hour

Input/Output

Reference Input	BNC (x2) (including loop-through), HD Tri-level sync (0.6 Vp-p/75 Ω/negative) or SD blackburst/composite sync (0.286 Vp-p/75 Ω/negative)
-----------------	--

Input/Output

HD-SDI Input	BNC (x1) (HD/SD switchable) HD-SDI: SMPTE 292M (w/embedded audio) SD-SDI: SMPTE 259M (w/embedded audio)
Analog Audio Input	XLR-type 3-pin (female) (x2) (channel selectable), +4/0/-3/-6 dBu (selectable), 10 k Ω , balanced
Digital Audio Input (AES/EBU)	BNC (x4), 8 ch (2 ch each, 1/2 ch, 3/4 ch, 5/6 ch and 7/8 ch), AES-3id-1995
Timecode Input	BNC (x1), SMPTE timecode, 0.5 Vp-p to 18 Vp-p/10 k Ω /unbalanced
System Timecode Input	BNC (x1), SMPTE timecode, 0.5 Vp-p to 18 Vp-p/10 k Ω /unbalanced
Analog Composite Output	BNC (x1), 1.0 Vp-p/75 Ω /negative, SMPTE 170M
HD-SDI Output	BNC (x2), 1: SMPTE 292M (w/embedded audio) 2: SMPTE 292M (w/embedded audio), character on/off
Monitor	DE-15 (x1), VGA
HD-SDI Monitor	BNC (x1), SMPTE 292M (w/embedded audio), character on/off
SD-SDI Monitor	BNC (x1), SMPTE 259M (w/embedded audio), character on/off
Analog Composite Monitor	BNC (x1), 1.0 Vp-p/75 Ω /negative, SMPTE 170M, character on/off
HDMI Monitor	Type-A (x1), 19 pin
Analog Audio Output	XLR-type 3-pin (male) (x2) (channel selectable), +4/0/-3/-6 dBu (selectable), 600 Ω , Lo-z, balanced
Analog Audio Monitor	XLR-type 3-pin (male) (x2), +4 dBu, 600 Ω , Lo-Z, balanced
Digital Audio Output (AES/EBU)	BNC (x4), 8 ch (2 ch each, 1/2 ch, 3/4 ch, 5/6 ch and 7/8 ch), AES-3id-1995
Headphone Output	JM-60 Stereo phone jack (x1), -13 dBu, 8 Ω , unbalanced
Timecode Output	BNC (x1), SMPTE timecode, 1.0 Vp-p/75 Ω /unbalanced
Video Control	D-sub 9-pin (female) (x1), EIA RS-423

Input/Output

Ethernet	RJ-45 (x1) 1000BASE-T: IEEE 802.3ab 100BASE-TX: IEEE 802.3u 10BASE-T: IEEE 802.3
Remote Input (9-pin)	D-sub 9-pin (female) (x2), RS-422A
Remote (GPIO)	D-sub 15-pin (female) (x1), Input: CMOS, Output: open-collector
Maintenance	USB (x5)
AC Input	AC Input (x1), 100 V to 240 V, 50/60Hz

Video Performance

Sampling Frequency	Y: 74.25 MHz, Pb/Pr: 37.125MHz
Quantization	8 bits/sample
Error Correction	Reed Solomon Code

Processor Adjustment Range

Video Level	$-\infty$ to +3 dB
Chroma Level	$-\infty$ to +3 dB
Set Up/Black Level	-30 IRE to +30 IRE/-210 mV to +210 mV
Chroma Phase	-30° to $+30^{\circ}$
System Sync Phase	-15 μ s to +15 μ s
System SC Phase	0 ns to 400 ns

Audio Performance

Sampling Frequency	48 kHz
Quantization	24 bits
Frequency Response	20 Hz to 20 kHz +0.5/-1.0 dB (0 dB at 1 kHz)
Dynamic Range	More than 90 dB
Distortion	Less than 0.05% (at 1 kHz)
Headroom	20/18/16/12/9 dB (selectable)

Other Equipment

Built-in Display	4.3-inch type color LCD monitor
Expansion Slot	PCI Express (x2), 8-lane

Supplied Accessories

Supplied Accessories

Operation manual (1)
Installation manual (1)

Notes

Note

*1 The values for dimensions are approximate.
*2 Playback and copy only.

Gallery



© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.