

BC-U2A

Two-channel simultaneous battery charger/AC adaptor for BP-U90/U60/U60T/U30 Lithium-ion battery



Overview

Charges two BP-U90/U60/U60T/U30 batteries

The BC-U2A battery charger can simultaneously charge two compact BP-U90, BP-U60 / 60T or BP-U30 Lithium-ion batteries at high speed

Built-in AC adaptor provides 12 V DC power output while charging one battery

The BC-U2A also has 12 V DC power output cable to power a camcorder directly, while charging one battery simultaneously.

Portable design for ease of use

The BC-U2A has a mass of 620 g (1 lb 6 oz) and dimensions (W x H x D) of 177 x 53.2 x 137 mm (7 x 8 1/8 x 5 1/2 inches).

NOTE: BC-U2A is compliant with safety standard IEC62368-1.

Specifications

General

Power Requirements	AC100V~240V 50/60Hz
--------------------	---------------------

Power consumption	89W
-------------------	-----

DC supply	[36W] 12V / 3.0A
-----------	------------------

Charging Voltage	16.4V
Dimensions (W x H x D)	177x53.2x137 (mm)
Mass	620 (g) +DC out cable
Operating Temperature	[DC supply]-5 °C~+45°C [Charge] 0°C~+45°C

Approximate charge times

BP-U90	190 minutes
BP-U60 / 60T	150 minutes
BP-U30	130 minutes

Supplied Accessories

Supplied Accessories	Instruction manual Warranty Paper DC out cable
----------------------	------------------------------------------------------

Related products



PXW-FS7M2

4K Super 35mm
Exmor CMOS sensor
XDCAM camera with



PXW-FS5

Grab and Shoot with
handheld Super 35



PXW-FS5M2

'Grab and shoot'
Super35 handheld
camcorder with



PXW-Z190

4K Handheld
Camcorder with all-
new 1/3-type 3CMOS
with 4K 50p/60p*
recording capability,

Variable ND Filter, E-Mount (Lever Lock), 4K/2K RAW and XAVC recording



MCX-500

Multi-Camera Live Producer

stunning new creative look, 4K 120fps HFR and HDR, α Mount lens system, Variable ND Filter, 4K/2K RAW and XAVC recording

25x zoom lens and advanced Face Detection AF

Gallery

