

## CBK-NA1

3G/4G/LTE and Wi-Fi network adapter kit for XDCAM camcorders



### Overview

#### **Optimises LAN connection for PXW-X180, PXW-X200 and PXW-X500 camcorders working with CBK-WA100 and CBK-WA101 wireless adapters**

The CBK-NA1 network adapter kit consists of a CBK-NA1E modem attachment for 3G/4G/LTE and Wi-Fi communication, and a CBK-NA1R USB/RJ-45 adapter. The CBK-NA1E allows you to attach the modem to the camcorder's handle to avoid interfering with the camcorder operation and to improve the signal transmission. The CBK-NA1R allows you to use the camcorder's streaming features with a wired connection. The unit has a cable clamp mechanism to avoid the USB connector being damaged by a cable stress.

#### **Network module extension adapter**

The CBK-NA1E allows you to attach a 3G/4G/LTE modem to a Sony camcorder and is optimised for the PXW-X180, PXW-X200 and PXW-X500 camcorders. The module is fixed on a 1/4-inch accessory shoe.

#### **USB/RJ-45 adapter**

The CBK-NA1R converts the USB terminal\* to the RJ-45 terminal of the camcorder or wireless adapter CBK-WA100 and CBK-WA101. It allows you to connect the camcorder to a network using a LAN cable for streaming with a wired connection. A cable clamp secures the USB connector.

\* The terminal name differs depending on the attaching device (USB wireless LAN module terminal or connecting terminal for external devices).

## Features

### **Network module extension adapter**

The CBK-NA1E allows you to attach a 3G/4G/LTE modem to a Sony camcorder and is optimised for the PXW-X180, PXW-X200 and PXW-X500 camcorders. The module is fixed on a 1/4-inch accessory shoe. The adapter allows you to avoid interfering with the camcorder operation and to improve the signal transmission.

### **USB/RJ-45 adapter**

The CBK-NA1R converts the USB terminal\* to the RJ-45 terminal of the camcorder or wireless adapter CBK-WA100 and CBK-WA101. It allows you to connect the camcorder to a network using a LAN cable for streaming with a wired connection. A cable clamp secures the USB connector. A supplied belt secures the network cable connected to the USB/RJ-45 adapter.

\* The terminal name differs depending on the attaching device (USB wireless LAN module terminal or connecting terminal for external devices).

## Specifications

### Network Module Extension Adapter: CBK-NA1E

USB	USB 2.0 Type A
Cable length	Approx. 200 mm (7 7/8 inches)
Mass	Approx. 65 g (2.3 oz)
Operating	

Operating temperature	0°C~+40°C
-----------------------	-----------

Operating humidity	20%~90%
--------------------	---------

Storage temperature	-20°C~+60°C
---------------------	-------------

## USB to RJ45 Adapter: CBK-NA1R

USB	USB 2.0 Type A
-----	----------------

Network terminal	RJ-45 10 /100BASE-T
------------------	---------------------

Feeding system	Bus power
----------------	-----------

Cable length	Approx. 100 mm (4 inches)
--------------	---------------------------

Mass	Approx. 20 g (0.7 oz)
------	-----------------------

Power consumption	1.5 W
-------------------	-------

Operating temperature	0°C~+40°C
-----------------------	-----------

Operating humidity	20%~90%
--------------------	---------

Storage temperature	-20°C~+60°C
---------------------	-------------

### Related products



**CBK-**



**CBK-**

## **WA100**

Wireless adapter for  
Camcorders and  
Decks [Mobile  
network 3G / 4G / LTE  
/Wireless LAN]

## **WA101**

Wireless adapter for  
PMW-400 and PXW-  
X320 [Mobile network  
3G / 4G / LTE /Wireless  
LAN]

## Gallery

