

SR-PC4

SRMASTER Data Transfer Unit



Overview

The SR-PC4* is an SRMemory data transfer unit specifically designed for portable environment. It can be smartly integrated into PC-based production environment such as on-set video village, on-set dailies system, and production office. Materials shot by the F65 can be instantly reviewed via SR-PC4's web-based GUI just after shooting.

* Please refer to brochure for supported formats

Features

- Fast Ingest
- Simple Viewing
- DC operation (AC adapter supplied)

Specifications

General	
Power Requirements	19.5 V DC
Operating Temperature	5°C to 35°C 41°F to 95°F
Storage Temperature	-20°C to +60°C -4°F to +140°F
Mass	3.9 kg 8 lb 10 oz
Dimensions (W x H x D) *1	88 x 250 x 231 mm (excluding protrusion) 3 1/2 x 9 7/8 x 9 1/8 inches (excluding protrusion)
Input/Output	
Monitor Output	BNC (x1) HD-SDI (1.485 Gbps) (SMPTE 292M, BTA-S004B standard) 3G-SDI (2.97 Gbps) (SMPTE 424M)
Network	RJ-45 jack (x1) 1000BASE-T
Option	PCI Express Slot (x1) (PCI Express x4 Gen1)

On-board Function

On-board Function	1D LUT, Down converter, Color space converter
-------------------	---

Confirmed Operational Environment

Browser	Firefox, Internet Explorer, Safari, Google Chrome
NFS Server	Redhat Linux E5, Mac OS v10.6
CIFS Server	Windows XP, Windows 7

Supplied Accessories

Supplied Accessories	AC adapter (1) Rubber feet (4) SR Viewer (CD-ROM) (1) Installation manual (1) Operation guide (1) Operation manual (CD-ROM) (1)
----------------------	--

Notes

Note	*1 The values for dimensions are approximate.
------	---

Gallery

