

## SNC-UNIHB

Outdoor fixed camera housing



### Overview

#### **13- inch outdoor aluminium housing with clear window and hinged opening**

Tamper resistant camera housing with lock down screws provided. High strength steel wall mount bracket included.

#### **Flexible positioning**

Designed for mounting to a flat wall or round pole, larger than 3.5- inches in diameter.

### Features

#### **Flexible positioning**

Designed for mounting to a flat wall or round pole, larger than 3.5- inches in diameter.

#### **All-weather operation**

The unit includes a AC 24V heater and blower.

#### **Supports a variety of cameras**

Network cameras accepted: Sony's SNC-CH120/CH140/CH220/CH240 cameras. Maximum camera/lens length should not exceed 9.5 inches.

## Related products



### **SNC- VB635**

Box-type 1080p/60 fps  
Camera with Half-inch  
Exmor™ CMOS Sensor  
Powered by IPELA  
ENGINE EX™ - V Series



### **SNC- VB630**

Box-type 1080p/60 fps  
Camera Powered by  
IPELA ENGINE EX™ - V  
Series



### **SNC- VB600**

Box-type 720p/60 fps  
Camera Powered by  
IPELA ENGINE EX™ - V  
Series



### **SNC- EB600**

Box-type 720p/30 fps  
Camera Powered by  
IPELA ENGINE EX™ - E  
Series



### **SNC- EB630**

Box-type 1080p/30 fps  
Camera Powered by  
IPELA ENGINE EX™ - E  
Series



### **SNC- EB520**

Box-type SVGA  
Camera - E Series

## Gallery

