

BKM-227W

NTSC / PAL input adaptor for LMD monitors



Overview

NTSC / PAL input adaptor for LMD monitors

Specifications

Input

Composite Input	BNC (x1), 1.0 Vp-p \pm 3 dB sync negative
-----------------	---

Y/C Input	Mini DIN 4-pin (x1) Y: 1.0 Vp-p \pm 3 dB sync negative, C: 0.286 Vp-p \pm 3 dB (NTSC burst signal level), 0.3 Vp-p \pm 3 dB (PAL, PAL-M burst signal level)
-----------	---

Output

Composite Output	BNC (x1), loop-through, with 75 ohms automatic termination
------------------	--

Y/C Output	Mini DIN 4-pin (x1), loop-through, with 75 ohms automatic
------------	---

termination

General

Voltage +3.3 V, +5 V DC (supplied from the main unit)

Power Consumption Approx. 1.8 W

Operating Temperature 0°C to 35°C
(Recommended: 20°C to 30°C)
32°F to 95°F
(Recommended: 68°F to 86°F)

Operating Humidity 0% to 90% (no condensation)

Storage/Transport Temperature -20°C to +60°C
-4°F to +140°F

Storage/Transport Humidity 0% to 90%

Operating/Storage/Transport Pressure 700 hPa to 1060 hPa

Dimensions (W x H x D) *[1] 100 x 20 x 162 mm
4 x 13/16 x 6 1/2 inches

Mass Approx. 240 g
Approx. 8.5 oz

Supplied Accessories

Operating Instructions (1)

Notes

Note

*[1] The values for dimensions are approximate.

Gallery

