

## SNC-XM631

Minidome 1080p/30 fps Camera  
Powered by IPELA ENGINE EX™ –  
X Series



### Overview

#### **Excellent Full HD picture quality in a compact, discreet indoor housing: ideal for retail, banking and education applications**

The SNC-XM631 minidome IP camera is suited to a wide range of indoor security and surveillance environments, from banks and retail spaces to schools and colleges.

It's compact and easy to install, vandal resistant with an IK10 rating for protection against tampering or deliberate damage.

Full HD picture quality is assured by the sensitive, high-resolution Exmor™ CMOS sensor that's teamed with Sony's latest-generation IPELA ENGINE EX™ signal processing system. Every scene looks clearer, sharper and more detailed – even in challenging low-light conditions or with harsh backlighting. Extra intelligence is added by DEPA Advanced Intelligent Video Analytics that can intelligently trigger an alarm based on user-defined rules.

Full HD pictures from the wide-angle (113 degree horizontal field of view) lens are fine-tuned by the advanced IPELA ENGINE EX™ processing engine. This delivers wide dynamic range and cuts noise for crisp, clear results – even in less-than-perfect lighting conditions. Built-in image stabilisation reduces the effects of

vibration, making it easier to see what's happening.

The camera supports image rotation, enabling a vertical image format also known as corridor view, ideal for video security and surveillance applications in corridors and hallways. This extra mode electronically flips the camera image through a quarter turn, presenting a correctly oriented 9:16 vertical 'portrait' view at Full HD resolution and no wasted pixels.

For even greater flexibility, there is a choice of three optional lenses to accommodate a wide range of (83°, 51° and 25°) horizontal viewing angle requirements.

## Features

### **See every detail with Full HD quality**

The sensitive, high-resolution Exmor CMOS sensor captures crisp, detail-packed Full HD (1920 x 1080) video images.

### **Wide angle lens**

A horizontal viewing angle of 113 degrees makes the camera ideal for wide area surveillance, requiring fewer cameras to cover the same space.

### **Latest generation imaging power**

High quality imaging is assured by Sony's unique IPELA ENGINE EX™ signal processing platform that combines powerful signal processing with intelligent video analytics technologies. XDNR (eXcellent Dynamic Noise Reduction) assures clear low-light images, while Visibility Enhancer (VE) dynamically optimises brightness and colour reproduction on a pixel-by-pixel basis. Extra intelligence is added by DEPA Advanced analytics with face detection that can trigger alarms based on user-determined rules.

### **Wide dynamic range**

Innovative View-DR technology achieves a dynamic range

equivalent to 90 dB, capturing objects clearly and adaptively – even with harsh backlighting or sun-drenched highlights.

### **Excellent low-light sensitivity**

The camera is capable of capturing clear images in very low light conditions: minimum illumination of 0.3 lx in Colour mode and 0.3 lx in B/W mode (at 50 IRE).

### **Better pictures, day or night**

Electronic Day/Night function automatically switches the camera between Day (colour) and Night (B/W) modes, depending on light levels.

### **Steadier, more stable images**

The in-built image stabiliser reduces the effects of camera shake or vibration for steadier images with reduced blur.

### **Optimum picture quality in any situation**

A choice of selectable picture modes optimises camera settings for best picture quality in a wide range of applications and lighting environments.

### **Recording quality to suit your network**

Select CBR (constant bitrate), VBR (variable bitrate) or VBR-with-cap compression modes for optimised recording quality depending on IP network conditions.

### **Automatic edge recording to memory card**

Edge Storage allows recording of video directly to an optional SD/SDHC card, even when a network connection isn't available.

### **Power over Ethernet**

The camera is powered using PoE (IEEE 802.3af) via a standard RJ-45 connector, simplifying installation and eliminating the need for additional power cables.

### **Easy mounting on wall or ceiling with three-axis**

## **lens adjustment**

This allows the lens unit to be turned in pan, tilt and rotate axes for versatile camera angle adjustment.

## **Easy, flexible field-of-view adjustments**

e-Varifocal allows electronic zooming and adjustment of field of view – for easy, flexible installation without cumbersome focus re-adjustment that’s needed with optical varifocal lenses.

## **Optional lenses for flexible control over field-of-view**

In addition to the camera’s supplied lens (with 113 degree horizontal viewing angle), three optional fixed lenses are also available with a horizontal viewing angle of 83 degrees, 51 degrees and 25 degrees respectively to allow flexible field-of-view camera settings.

## **Vandal resistant design**

The camera is vandal resistant with an IK10 impact rating, for protection against destructive behaviours.

## **View with your smartphone**

Securely access the camera using a smartphone or tablet (Android or iOS) to view images and control pan/tilt/zoom functions remotely.

## **Easy IP network configuration**

Configuration of network settings is made quick and simple using the supplied SNC Easy IP Setup application.

## **ONVIF (Open Network Video Interface Forum) compliance**

Support for ONVIF simplifies integration with a wide range of VMS platforms and hardware, providing video streaming and camera control. ONVIF (Open Network Video Interface Forum) defines a common protocol for the exchange of information between network video devices, including automatic device discovery and

video streaming.

## Specifications

### Camera

Image Sensor	1/2.9-type progressive scan Exmor CMOS sensor
Number of Effective Pixels	Approx. 2.14 Megapixels
Minimum Illumination (50 IRE)	Color: 0.3 lx (F2.0, View-DR Off, VE Off, AGC On, 1/30 s, 30 fps) B/W: 0.3 lx (F2.0, View-DR Off, VE Off, AGC On, 1/30 s, 30 fps)
Minimum Illumination (30 IRE)	Color: 0.18 lx (F2.0, View-DR Off, VE Off, AGC On, 1/30 s, 30 fps) B/W: 0.18 lx (F2.0, View-DR Off, VE Off, AGC On, 1/30 s, 30 fps)
Dynamic Range	Equivalent to 90 dB with View-DR technology
Gain	Auto
Shutter Speed	1/1 s to 1/10,000 s
Exposure Control	Exposure compensation, Shutter speed
	ATW, ATW-PRO, Indoor, Outdoor,

White Balance	Fluorescent lamp, Mercury lamp, Sodium vapour lamp, Metal halide lamp, White LED, One push WB, Manual
Lens	Fixed lens
Zoom Ratio	Digital zoom 4x Total zoom 4x
Horizontal Viewing Angle	113°
Vertical Viewing Angle	61°
Viewing Tilt Angle	151°
Focal Length	f = 2.8 mm
F-Number	F2.0
Minimum Object Distance	500 mm
Pan/Tilt/Rotation Angle (manual)	0° to 350° 0° to 60° -175° to +175°
<h2>Camera Features</h2>	
Day/Night	Electronic D/N
e-Flip	Yes

Image rotate	90°, 270°
Mirroring	Yes
Wide-D	View-DR
Tone Correction	Visibility Enhancer
Noise Reduction	XDNR
Image Stabilizer	Electronic
Picture Mode	Yes
Privacy Masking (number)	20
Privacy Masking (shape)	Quadrangle formed by any four corner points
Privacy Masking (color/effect)	Opaque 14 colors (Black, White, Red, Green, Blue, Cyan, Yellow, Magenta, Gray (6 scales)), Mosaic
Edge Storage	Yes
Compatibility with Cloud Service	Yes
Vandal Resistant	IK10
	3 independent positions for characters (Codec, Date & Time,

Superimpose Number	Event, Text (Max. 64 characters)), 1 independent position for a logo mark
Superimpose Language	English
Menu Language	English, Japanese, Chinese (simplified), Chinese (traditional), French, Spanish, German, Italian, Korean, Portuguese, Russian, Arabic, Hindi, Vietnamese, Thai, Turkish, Polish
Smartphone viewer	Yes
<b>Video</b>	
Resolution	1920 x 1080, 1280 x 720, 1024 x 576, 720 x 576, 720 x 480, 704 x 576, 640 x 480, 640 x 360, 352 x 288, 320 x 184 (H.264, JPEG)
Compression Format	H.264 (High/Main/Baseline Profile), JPEG
Maximum Frame Rate	H.264: 30 fps (1920 x 1080) JPEG: 30 fps (1920 x 1080)
Bitrate Control Mode	CBR/VBR (selectable)



Range of Bit Rate Setting	64 Kbps to 32 Mbps
Solid PTZ	Yes
e-Varifocal	Yes
Adaptive Rate Control	H.264
Bandwidth Control	JPEG
Multi streaming Capability	Yes (3)
Number of Clients	20

## Intelligent Video/Audio Analytics

Analytics Architecture	DEPA Advanced
Intelligent Motion Detection	Yes
Face Detection	Yes
Tamper Alarm	Yes
Scene Analytics	Passing, Intrusion, Left Object Detection, Removed Object Detection

## System Requirements

Operating System	Windows XP (32 bit) Professional Edition Windows Vista (32 bit) Ultimate, Business Edition Windows 7 (32/64 bit) Ultimate, Professional Edition Windows 8 Pro (32/64 bit) Windows 8.1 Pro (32/64 bit)
Processor	Intel Core i7 2.8 GHz or higher
Memory	2 GB or more
Web Browser	Microsoft Internet Explorer Ver. 7.0, Ver. 8.0, Ver. 9.0, Ver. 10.0, Ver. 11.0 Firefox Ver. 19.02 (plug-in free viewer only) Safari Ver. 5.1 (plug-in free viewer only) Google Chrome Ver. 25.0 (plug-in free viewer only)
SNC toolbox	Yes
SNC toolbox mobile	Yes

## Network

IPv4, TCP, UDP, ARP, ICMP, IGMP\*, HTTP, DHCP, DNS, NTP, RTP/RTCP, RTSP over TCP, RTSP over HTTP,

Protocols	SMTP, IPv6, HTTPS, FTP (client), SNMP (v1, v2c, v3), SSL *SSM (Source Specific Multicast) is supported.
Number of IP Address/Mac ADDRESS	1
QoS	DSCP
Multicast Streaming Support	Yes
ONVIF Conformance	Profile S, Profile T
Authentication	IEEE802.1X

## Interface

Network Port	10BASE-T/100BASE-TX (RJ-45)
Alarm Input (Sensor Input)	x1, make contact, break contact
Alarm Output	x1, +/- 50 V, 0.4 A (solid state relay outputs electrically isolated from the camera)
Card Slots	SD x 1
Confirmed SD Card	Max. 64 GB

Type

## General

Power Requirements IEEE 802.3af compliant (PoE system)

Power Consumption 4.0 W max.

Operating Temperature -10°C to +50°C  
14°F to 122°F

Cold Start Temperature 0°C  
32°F

Storage Temperature -30 °C to + 60 °C  
-22 °F to + 140 °F

Operating Humidity 20 % to 80 %

Storage Humidity 20 % to 80 %

Dimensions \*1  $\phi 104.5 \times 56.5$  mm  
 $\phi 4 \frac{1}{8}$  inches x 2  $\frac{1}{4}$  inches

Mass Approx. 200 g  
Approx. 7.1 oz

External Material Top cover/Dome cover : PC  
(Polycarbonate)  
Lower case:AL Die-cast

External Color Top cover: Munsell 4.4 BG 8.4/0.2

Fire Retardant	UL2044
Safety Regulations	<p>JATE Technical standard (LAN)          UL2044, IEC60950-1 (CB)          VCCI (Class A), FCC (Class A), IC (Class A)          Emission: EN55022 (Class A) + EN50130-4          Immunity: EN55022 (Class A) + EN55024          Emission: AS/NZS CISPR22 (Class A)          EMC-TR</p>
Supplied Accessories	<p>CD-ROM (supplied programs) (1)          Installation Manual (1)          Template (1)          Safety regulations (1)          Warranty booklet (1)          I/O cable (1)</p>
Optional Accessories	<p>SNCA-L038MF (M12 Mount Lens)          SNCA-L060MF (M12 Mount Lens)          SNCA-L120MF (M12 Mount Lens)</p>

## Notes

\*1 The values for dimensions are approximate.

## Related products



### **FWL- 65W855C**

65" BRAVIA  
Professional Full HD  
Colour LED Display



### **FWL- 75W855C**

75" BRAVIA  
Professional Full HD  
Colour LED Display



### **FWL- 55W805C**

55" BRAVIA  
Professional Full HD  
Colour LED Display



### **FWL- 40W705C**

40" BRAVIA  
Professional Full HD  
Colour LED Display



### **FWL- 48W705C**

48" BRAVIA  
Professional Full HD  
Colour LED Display

## Gallery

