

UNI-INL7C2

Normal pendant camera housing



Overview

White pendant indoor camera housing clear dome

The UNI-INL7C2 is an Indoor Pendant Mount Housing for SNC-RH124, RS44N, RS46N, RX-Series, RZ25N. Optically correct polycarbonate clear lower dome.

No electronics. The user should provide AC 24V feeds to the camera/enclosure.

Clear view

7-inch diameter clear polycarbonate lower dome.

Features

Pendant

White trim ring on a dome semi-flash/ pendant ceiling housing. 1 1/2-inch NPT quick connect coupling.

Gallery

