

## LMP-C162

Replacement lamp for the VPL-CS20A/CX20A and VPL-ES3/EX3 LCD business projectors



### Overview

#### **165W UHP replacement lamp for the VPL-CS20A/CX20A and VPL-ES3/EX3 LCD business projectors**

For the VPL-CS20A/CX20A and VPL-ES3 LCD business projectors.

#### **Lamp replacement notification**

A -inchplease replace the lamp-inch message is displayed when it is time to replace the lamp.

### Features

#### **Replacement lamp**

For the VPL-CS20A/CX20A and VPL-ES3 LCD business projectors

#### **Lamp replacement notification**

The projector alerts you when the lamp needs to be replaced. A -inchplease replace the lamp-inch message is displayed when it is time to replace the lamp. The message disappears when any key on the remote commander or control panel is pressed.

#### **Selectable lamp wattage**

The lamp is switchable between 165W (High Mode) 125W (Std Mode) and lasts for 2000 hours.

## Gallery

