


## NXLK-IP45F

AV Multiplexer/Demultiplexer Board



**NETWORKED LIVE**

### Overview

#### **Ideal for handling audio and video signals in IP-based live production environment**

The NXLK-IP45F AV Multiplexer/Demultiplexer Board is capable of multiplexing or demultiplexing audio and video over IP. The board separates audio over IP and video over IP signals from video over IP or SDI inputs, or combines both into an SDI with embedded audio signal.

#### **Interconnects SDI-based equipment with IP-based infrastructure**

Option board for the NXL-FR318 Signal Processing Unit

#### **Video and audio format flexibility**

The board provides support for Dante audio over IP format and can handle both HD and 4K video formats.

### Features

#### **Audio over IP and video over IP multiplexer**

The NXLK-IP45F multiplexes audio over IP and video over IP signals and outputs an SDI signal with embedded audio.

#### **Audio over IP and video over IP demultiplexer**

The board demultiplexes audio from video over IP or an SDI signal with embedded audio and outputs separate audio over IP and video over IP signals.

## SDI to IP conversion

The board is capable of converting SDI to IP under demultiplexer mode.

## Supports major audio over IP format

The board provides support for Dante audio over IP format.

## Supports HD/4K

The board can handle both HD and 4K video formats.

## Specifications

### General specifications

|                    |  |
|--------------------|--|
| Power supply       | DC 12 V (supplied from NXL-FR318)  |
| Power consumption  | 2.5 A 30 W (3 slot occupancy)  |
| Dimensions         | Main board: 114.5 × 28 × 275.8 mm (4 5/8 × 1 1/8 × 10 7/8 in.) (W × H × D)<br>Connector board: 131 × 35.2 × 117.25 mm (5 1/4 × 1 7/16 × 4 5/8 in.) (W × H × D) |
| Mass               | Main board: Approx. 244 g (8.6 oz)   |
| Connector board    | Approx. 250 g (8.8 oz)   |
| Temperature ranges | Operation guaranteed temperature: 5 °C to 40 °C (41 °F to 104 °F)<br>Performance guaranteed temperature: 10 °C to 35 °C (50 °F)                                |

to 95 °F)  
 Storage temperature: -20 °C to +60 °C (-4 °F to +140 °F)

## I/O specifications

|                 |  |
|-----------------|--|
| Connector       | BNC type 75 Ω  |
| Number of lines | Input/output: 4<br>Output: 4   |
| Signal formats  | SMPTE ST 424   |
| Connector       | SFP+   |
| Number of lines | 2  |
| Signal formats  | 10GBASE-** (dependent on SFP+ transceiver module)<br>For details on supported SFP+ transceiver modules (e.g., OTM-10GSR1), contact your local Sony service representative. |
| Connector       | RJ-45  |
| Number of lines | 2  |
| Signal formats  | 1000BASE-T   |

## Supplied accessories

\*

Operation manual (1)

## Supported formats

SDI input/output

3840 x 2160 59.94p Level-A, 2SI or SQD, LLVC compression

3840 x 2160 50p Level-A, 2SI or SQD, LLVC compression

## Related products



NETWORKED LIVE

### **PWS-110NM1**

IP Live System Manager Station



NETWORKED LIVE

### **OTM-10GSR1**

10GBASE-SR SFP+ Transceiver for Sony Networked Media Interface products



NETWORKED LIVE

### **NXL-FR316**

SDI-IP signal processing unit



NETWORKED LIVE

### **NXLK-IP40F**

SDI-IP converter board with 3G-SDI and SFP+ ports



### **BPU-4800**

4K / HD baseband processor unit and UHFR server for HDC-4800 system camera

## Gallery

