

SNCA-CEILING

Mounting coupling for pendant applications



Overview

Features;

- The coupling is mounted to the ceiling. SNCA-POLE30 is threaded into the coupling and the camera housing connected to the bottom of the pipe.
- The base has an input for electrical conduit (1/2" or 12.7 mm)

Related products



SNC-EB600

Box-type 720p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



SNC-EB600B

Basic Box-type 720p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



SNC-EB630

Box-type 1080p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



SNC-EB630B

Basic Box-type 1080p/30 fps Camera Powered by IPELA ENGINE EX™ - E Series



SNC-VB600

Box-type 720p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



SNC-EP521

Standard Definition (PAL) PTZ Network Camera



SNC-EP580

1080p/30 fps PTZ Camera - E Series



SNC-ER521

Standard Definition (PAL) Rapid Dome Network Camera



SNC- ER550

720p/30 fps Rapid
Dome Camera - E
Series



SNC- ER580

1080p/30 fps Rapid
Dome Camera - E
Series



SNC- ER585

Outdoor Unitized
1080p/30 fps Rapid
Dome Camera - E
Series

Gallery

