

## PXW-Z450

4K HDR 2/3-type CMOS sensor shoulder camcorder with advanced network features, low power consumption and optimised weight balance



### Overview

#### **World's first 4K HDR shoulder camcorder**

Sony's ground-breaking PXW-Z450 combines 4K resolution (3840 x 2160) with superbly balanced shoulder-mount ergonomics and a versatile 2/3-inch B4 lens mount. It's a robust, high performance acquisition tool for 4K and HD news, documentaries, live events and general field production.

The PXW-Z450 records 4K QFHD (3840x2160) at 50p/59.94p, with 4K Slow and Quick motion up to 59.94p\*, as well as a variety of HD formats including XAVC Intra, XAVC Long GOP, MPEG HD 422 and MPEG HD 420. The Z450 can record and output not only SDR but also HDR pictures as Hybrid Log Gamma (HLG) and S-Log3 with BT.2020 colour space\*.

Thanks to a specially-developed 4K 2/3-type Exmor R CMOS sensor, the PXW-Z450 allows you to use a wide range of commercially-available B4 mount lenses without having to use an adapter. The PXW-Z450 offers the same advanced features as the PXW-X400 Full HD camcorder, with exceptional weight balance and low power consumption, alongside excellent networking features.

#### **4K HDR / HD SDR simultaneous recording**

The Z450 can record both 4K HDR and HD SDR simultaneously to support high speed workflows.\* No need to spend time converting 4K HDR clips to HD SDR to get on-air quickly.

#### **Advanced picture monitoring\***

To make HDR production easier, picture quality can be monitored with BT.709 imagery in the viewfinder while shooting S-Log3 or HLG, while a high quality Focus Magnifier picture can be made from the 4K resolution image.

#### **Versatile B4 ENG lens options**

Thanks to a versatile 2/3-type native sensor and B4 lens mount, this camcorder allows you to install a variety of B4 ENG lenses including either 4K or HD. This flexible lens options supports a variety of shooting applications while saving cost.

#### **Low power and ergonomic design**

Z450 power consumption is as low as 24W in normal operation (XAVC recording with colour LCD on), extending recording times, while an ergonomically balanced weight distribution eases operator fatigue and enhances stable shooting.

#### **Excellent connectivity and wireless functions [online]**

The PXW-Z450 enables robust, high-speed ENG/EFP workflows with high resolution clip or proxy clip transfer via Wired / Wireless LAN or 4G/LTE connection. The camcorder

can also stream HD video to a receiver even while shooting in 4K.

\* Version 3.0 firmware upgrade required.

## Features

### **High quality recordings in 4K QFHD and HD**

The PXW-Z450 supports a variety of 4K and HD formats, including 4K QFHD (3840x2160) at 50p/59.94p, using the XVAC Intra and XAVC Long GOP, MPEG HD 422 and MPEG HD 420 workflow standards.

### **4K Slow and Quick motion**

The camcorder provides 4K Slow and Quick motion up to 59.94p\*.

\* Version 3.0 firmware upgrade required.

### **High sensitivity image making**

The camcorder's specially-developed 4K 2/3-type Exmor R CMOS sensor provides superb image quality and high sensitivity. The sensor matches B4 mount lens systems, allowing you to use commercially-available B4 4K/HD lens systems without needing an adapter.

### **4K HDR / HD SDR simultaneous recording to one card**

The PXW-Z450 supports simultaneous 4K HDR and HD SDR recordings to a single card\* and Hybrid Log Gamma (HLG) and S-Log3 recordings with BT.2020 colour space.\*

\* Version 3.0 firmware upgrade required.

### **Quad Link 3G-SDI option for 4K 50p/59.94p output\*\***

Use the PXW-Z450's four 3G-SDI connectors to support 4K 50p/59.94p output as a Quad Link 3G-SDI signal. Connect any 4K Quad Link product you want to the PXW-Z450.

\*\* Version 2.0 firmware required plus CBKZ-Z450QL upgrade license.

### **4K cache recordings\***

The PXW-Z450 provides cache recording support for 4K pictures at XAVC-Long GOP quality.

\* Version 3.0 firmware upgrade required.

### **Discover optimised weight balance**

Thanks to its fine-tuned ergonomic design, the PXW-Z450 camcorder achieves an optimised weight balance to lessen the weight on the lens grip and support stable image shooting.

### **Supports Full HD OLED viewfinders**

The PXW-Z450 supports a variety of Sony's viewfinders, including the Full HD OLED HDVF-EL30 and HDVF-EL20. The OLED viewfinders take an advantage of focusing the 4K shooting.

### **Advanced picture monitoring\***

Picture quality can be monitored with BT.709 pictures in the viewfinder while shooting S-Log3 or HLG, while a high quality Focus Magnifier picture can be made from the 4K resolution image.

\* Version 3.0 firmware upgrade required.

**Embedded RJ-45 connector**

An embedded RJ-45 Ethernet 100B-T connector on the right side of the camcorder provides a robust and fast network connection that can be used for file transfer, live streaming and camera control from a web browser.

**One-touch wireless LAN connection**

A Near Field Communication (NFC) function allows easy, one-touch wireless LAN connection to a smartphone or tablet device without manual setting of the network parameters.

**Built-in wireless module with Content Browser Mobile™**

The camcorder’s built-in wireless module gives you more mobility with no cable needed, enabling proxy recording and file transfer or live streaming. In file transfer mode, high-resolution files and XAVC Proxy files can be transferred over wireless connection to cloud or FTP server thanks to Content Browser Mobile\*\*\* (CBM) application. In Push mode, the CBM application enables users to monitor the currently shot video and to wirelessly control camcorder settings such as focus, zoom, iris, white balance, REC START/STOP, and more. With Content Browser Mobile V2.0 proxy trim, proxy partial clip upload, and logging are available. High quality live streaming is provided by the advanced Sony QoS technology embedded in the camcorder and in the PWS-100RX1 network RX station. Non QoS live streaming is also possible with a third-party receiver or VLC player.

\*\*\* The CBM application can be downloaded from the Google Play Store or App Store.

**Support for DWX wireless microphone systems\***

The PXW-Z450 supports Sony’s DWX series wireless microphone systems. Power Save Mode synchronises with Camera Power OFF and can be controlled by assignable buttons. With power save enabled, the status is displayed in the viewfinder.

\* Version 3.0 firmware upgrade required.

**Easy network connection**

A dedicated button gives simple on-off control of Network Client Mode, Auto Upload (Proxy) and Live Streaming. Proxy recording mode can be enabled or disabled by assignable buttons\*. Wi-Fi Access Point for Station Mode can be set by the camera menu\*. Multiple CCM addresses can be saved on-board\*.

\* Version 3.0 firmware upgrade required.

**Records a second camera’s feed via SDI**

An SD or HD-SDI (up to 1.5G) signal can be recorded by the camcorder, a useful function to record an external feed from another camera.

**Lower power consumption**

Due to advanced component design, the PXW-Z450’s power consumption is as low as 24 W in normal recording mode\*\*. This reduces battery consumption and extends recording times.

\*\* XAVC recording with colour LCD on.

Specifications

General

	Approx. 3.6 kg (body only without lens, VF, Mic)
Mass	Approx. 7 lb 15 oz

	(body only without lens, VF, Mic)
Dimensions (W x H x D) *1	170x 269 x 332 mm (excluding protrusions, body only)  6 3/4 x 10 5/8 x 13 1/8 inches (excluding protrusions, body only)
Power Requirements	DC 12 V (11 V to 17.0 V)
Power Consumption	Approx. 24 W (while XAVC recording, color LCD on)  Approx. 26 W (while XAVC recording, color LCD on)
Operating Temperature	0° C to 40° C 32° F to 104° F
Storage Temperature	-20°C to +60°C -4°F to +140°F
Continuous Operating Time	Approx. 160 min with BP-FLX75
Recording Format (Video)	XAVC Intra:  - XAVC-I QFHD 300 mode: MPEG-4 AVC/H.264, CBG, Max.600Mbps  - XAVC-I HD 100 mode: MPEG-4 AVC/H.264, CBG, Max.223Mbps  XAVC Long: br>- XAVC-L QFHD 150 Mode: MPEG-4 AVC/H.264, VBR, Max. 150Mbps  XAVC Long: XAVC-L QFHD 100 Mode: MPEG-4 AVC/H.264, VBR, Max. 100Mbps  - XAVC-L422 HD 50 Mode: MPEG-4 AVC/H.264, VBR, Max. 50Mbps  - XAVC-L422 HD 35 Mode: MPEG-4 AVC/H.264, VBR, Max. 35Mbps  - XAVC-L422 HD 25 Mode: MPEG-4 AVC/H.264, VBR, Max. 25Mbps
Recording Format (Video)	MPEG HD422:  - HD422 mode: MPEG-2 422P@HL, CBR, Max.50 Mbps  MPEG HD:  - HQ mode: MPEG-2 MP@HL, VBR, Max.35 Mbps

	<p>MPEG IMX: - MPEG-2 422@ML, CBR, 50 Mbps</p> <p>DVCAM: - CBR, 25 Mbps</p>
Recording Format (Audio)	<p>XAVC Intra: LPCM 24 bits, 48 kHz, 4 channels XAVC Long: LPCM 24 bits, 48 kHz, 4 channels MPEG HD422: LPCM 24 bits, 48 kHz, 4 channels MPEG HD: LPCM 16 bits, 48 kHz, 4 channels MPEG IMX: LPCM 16/24 bits, 48 kHz, 4 channels DVCAM: LPCM 16 bits, 48 kHz, 4 channels</p>
Recording Format (Proxy Video)	<p>XAVC Proxy: AVC/H.264 Main Profile 4:2:0 Long GOP, VBR 1280 × 720, 9 Mbps (Target Rate) 1280 × 720, 6 Mbps (Target Rate) 640 × 360, 3 Mbps (Target Rate) 480 × 270, 1 Mbps, 500 kbps (Target Rate)</p>
Recording Format (Proxy Audio)	<p>XAVC Proxy: AAC-LC, 128 kbps, 2 channels</p>
Recording Time (Continuity) (XAVC Intra, XAVC Long) *2	<p>XAVC-I QFHD 300 mode: Approx. 20 min. with 128 GB SxS card at 59.94p</p> <p>XAVC-I HD 100 mode: Approx. 120 min. with 128 GB SxS card at 59.94i</p> <p>XAVC-L QFHD 150 mode: Approx. 80 min. with 128 GB SxS card at 59.94P</p> <p>XAVC-L QFHD 100 mode: Approx. xx min. with 128 GB SxS card at 59.94P</p> <p>XAVC-L422 HD 50 mode: Approx. 240 min. with 128 GB SxS card at 59.94i</p> <p>XAVC-L422 HD 35 mode: Approx. 340 min. with 128 GB SxS card at 59.94i</p> <p>XAVC-L422 HD 25 mode: Approx. 440 min. with 128 GB SxS card at 59.94i</p>
Recording Time (Continuity)	<p>MPEG HD422 mode: Approx. 240 min. with 128 GB SxS card at 59.94i</p>

(MPEG-2 HD422/HD420) *2	MPEG HD420 HQ mode: Approx. 360 min. with 128 GB SxS card at 59.94i
Recording Time (Continuity) (MPEG IMX 50M) *2	Approx. 240 min. with 128 GB SxS card at 59.94i
Recording Time (Continuity) (MPEG HD) *2	HD HQ Mode: Approx. 400 min. with 128 GB SxS card at 59.94i  HD SP Mode: Approx. 560 min. with 128 GB SxS card at 59.94i
Recording Time (Continuity) (DVCAM) *2	Approx. 440 min. with 128 GB SxS card at 59.94i
	XAVC Intra (XAVC-I QFHD 300 mode): - 3840 × 2160: 59.94p, 50p, 29.97p, 25p, 23.98p  XAVC Intra (XAVC-I HD 100 mode): - 1920 × 1080: 59.94p, 50p, 59.94i, 50i, 29.97p, 25p, 23.98p - 1280 × 720: 59.94p, 50p
Recording Frame Rate	XAVC Long (XAVC-L QFHD 150 mode): - 3840 × 2160: 59.94p, 50p  XAVC Long (XAVC-L QFHD 100 mode): - 3840 × 2160: 29.97p, 25p, 23.98p  XAVC Long (XAVC-L422 HD 50 mode): - 1920 × 1080: 59.94p, 50p, 59.94i, 50i, 29.97p, 25p, 23.98p - 1280 × 720: 59.94p, 50p
	XAVC Long (XAVC-L422 HD 35 mode): - 1920 × 1080: 59.94p, 50p, 59.94i, 50i, 29.97p, 25p, 23.98p  XAVC Long (XAVC-L422 HD 25 mode): - 1920 × 1080: 59.94i, 50i
	MPEG HD422: - 1920 × 1080: 59.94i, 50i, 29.97p, 25p, 23.98p - 1280 × 720: 59.94p, 50p, 29.97p, 25p, 23.98p
Recording Frame Rate	MPEG HD420: - 1920 × 1080: 59.94i, 50i, 29.97p, 25p, 23.98p - 1440 × 1080: 59.94i, 50i - 1280 × 720: 59.94p, 50p  MPEG IMX: - 720 × 486: 59.94i

- 720 × 576: 50i

DVCAM:

- 720 × 480: 59.94i

- 720 × 576: 50i

## Lens

Lens Mount Sony 2/3-inch type bayonet mount

## Input/Output

Genlock Input BNC (x1), 1.0 Vp-p, 75 Ω, unbalanced

Timecode Input BNC (x1), 0.5 V to 18 Vp-p, 10 kΩ

SDI Input SMPTE ST292/ST259 standard compliant, 4-channel audio  
1.5G  
Poolfeed Recording (upto 1080 59.94i)

Audio Input CH1/CH2: XLR-type 3-pin (female) (x2), Line/Mic/Mic/+48V selectable  
LINE: +4, 0, -3 dBu  
AES/EBU: AES3 compliant  
MIC: -70 dBu to -30 dBu

Mic Input XLR-type 5-pin, female: -70 dBu to -30 dBu

WRR (Wireless Microphone Receiver) D-sub 15-pin  
Analog CH1: -40 dBu  
Digital CH1/CH2: -40 dBFS

SDI Output Output 1/2/3/4: BNC (x4), 0.8 Vp-p,

Video Output BNC, SD analog composite/HD-Y selectable

Audio Output XLR-type 5-pin, male, +4/0/-3 dBu (balanced)

Timecode Output BNC, 1.0 Vp-p, 75 Ω

Earphone Output Stereo mini jack (x1)  
-11 dBu reference level output, maximum monitor volume, 16 Ω load

Speaker Output Monaural, 300 mW output

DC Input XLR-type 4-pin, male, 11 V to 17 V DC

DC Output Round type 4-pin, 11 V to 17 V DC, 1.8 A maximum rated current

Lens 12-pin, lens power source (11 V to 17V DC, 1.0 A maximum rated current)

Remote 8-pin

Light 2-pin

Camera Adaptor D-sub, 50-pin (x1)

Ethernet	RJ-45 (x1), 100BASE-TX: IEEE 802.3u, 10BASE-T: IEEE 802.3
USB	USB 3.0/2.0 4-pin (type A), USB2.0 4-pin (type B), USB2.0 4-pin (type-A)
HDMI	A type, 19-pin (x1)
Viewfinder	20-pin IF for HDVF Series Viewfinder, and 26-pin IF for CBK-VF02, HDVF-L750

### Audio Performance

Frequency Response	20 Hz to 20 kHz ( $\pm 3$ dB or less)
Dynamic Range	90 dB (typical)
Distortion	0.08% or lower (-40 dBu input level)
Headroom	20 dB (factory default) (20, 18, 16, 12dB), EBUL

### Camera Section

Imager	2/3-type "Exmor R" 4K CMOS
Effective Picture Elements	3840 (H) x 2160 (V)
Built-in Optical Filters	1: Clear, 2: 1/4ND, 3: 1/16ND, 4: 1/64ND
Shutter Speed (Time)	59.94i/p, 50i/p: 1/60 sec. to 1/2000 sec. + ECS 29.97p: 1/40 sec. to 1/2000 sec. + ECS 25p: 1/33 sec. to 1/2000 sec. + ECS 23.94p: 1/32 sec. to 1/2000 sec. + ECS
Shutter Speed (Slow Shutter(SLS))	2, 3, 4, 5, 6, 7, 8, 16-frame accumulation
Slow & Quick Motion Function	1080p: Frame rate selectable from 1fps to 60 fps
Sensitivity (2000 lx, 89.9% reflectance)	F10 (typical) (1920 x 1080/59.94i mode or 3840 x 2160/59.94p mode) F11 (typical) (1920 x 1080/50i mode or 3840 x 2160/50p mode)
Minimum Illumination	0.019 lx (F1.4, +42 dB, 16-frame accumulation)
White Balance	Preset (3200K), Memory A, Memory B/ATW
Gain Selection	-9, -6, -3, 0, 3, 6, 9, 12, 18, 24, 30, 36, 42 dB(TBD)
S/N Ratio	61 dB typical (typical, 1920x1080/59.94i mode, Noise Suppression On)



Viewfinder

Viewfinder	Option
------------	--------

Other Equipment

Built-in LCD Monitor	Color LCD, Screen size: 8.8 cm (3.5 inch) diagonal *3 , Aspect ratio: 16:9, Number of pixels: 960 (H) × 540 (V) for Video display, Audio level, TC, battery and media remaining capacity
Built-in Speaker	(x1)
Media SxS Card Slots	Number of slots: 2
Media SD Card Slots	Proxy (1), Utility (1)
GPS	Yes
Built-in Network Module	Yes
NFC	Yes

Supported Media

High Resolution Video/Audio	SxS card XQD card (with XQD ExpressCard Adapter, QDA-EX1) SDXC card (with XQD ExpressCard Adapter, MEAD-SD02)
Proxy Video/Audio and Utility	SDXC/SDHC

Supplied Accessories

Supplied Accessories	Shoulder Belt (1) Cold Shoe Kit (1) Lens Mount Cap (1) USB wireless LAN module (IFU-WLM3) (1) Protective Cap (2) Operation Guide (1) Operation Manual (CD-ROM) (1)
----------------------	--

Notes

*1	The values for dimensions are approximate.
*2	Recording time may vary by the encoding format or the type of memory.
*3	Viewable area measured diagonally.



**DWR-S02D**

Digital wireless receiver



**LMD-A220**

22-inch cost-effective, lightweight Full HD high grade LCD monitor for studio and field use



**CBK-WA02**

5GHz/2.4GHz Wireless LAN Adapter



**HDVF-L10**

3.5" Colour LCD HD Viewfinder



**IFU-WLM3**

USB wireless LAN module



**LMD-A170**

17-inch cost-effective, lightweight Full HD high grade LCD monitor for studio and field use



**LMD-B170**

17-inch cost-effective, lightweight basic grade Full HD LCD monitor for versatile use



**PWS-110RX1**

Network RX Station for XDCAM camcorders live streaming over 4G/LTE and Wi-Fi



**LMD-A240**

24-inch cost-effective, lightweight Full HD high grade LCD monitor for studio and field use



**LMD-B240**

24-inch cost-effective, lightweight basic grade Full HD LCD monitor for versatile use



**URX-S03D**

UWP-D two-channel slot-in receiver



**HDVF-EL30**

OLED 0.7-inch colour Full HD viewfinder with 3.5-inch sub-LCD



**HDVF-EL20**

OLED 0.7-inch colour HD viewfinder



**CBK-VF02**

3.5" Colour LCD HD Viewfinder for PXW-X500



**BP-FLX75**

Olivine long-lasting battery with 76 Wh capacity



**CBK-SP01**

Optional Soft Shoulder Pad

## Gallery

