

## VPL-EW255

3,200 lumens WXGA portable projector with wireless connectivity



### Overview

**Bring learning to life with this bright, energy-efficient, wireless-ready portable projector that has been designed in consultation with teachers and made for today's classrooms**

Combining superb widescreen WXGA image quality with smart energy-efficient features, the VPL-EW255 portable projector enhances learning with powerful presentations that really stand out. Simple to use and wireless ready, the projector is ideal for maximising student engagement in today's networked classrooms, making it your ideal partner throughout the busy school day.

Sony BrightEra™ panel technology assures clear pictures in any conditions, from daylight to darkened classrooms. Plenty of interfaces allow easy connection, while a choice of Picture Modes optimises viewing with any source – slide presentations, PC documents, pictures or videos. Adding an optional Wi-Fi module lets students and teachers wirelessly share homework, images and graphics from mobile devices like smartphones and tablets. There's a wide range of smart energy-saving features built in. And with a recommended lamp replacement time of 10,000 hours, downtime and maintenance costs are minimised.

## Features

### **Energy efficient with long-lasting lamp of 10,000 hours**

The lamp driver optimally controls the wattage of the lamp and achieves a long-lasting lamp time of 10,000\* hours. The recommended lamp replacement time is extended by 43%, compared to the previous model.

\*Lamp mode: low, Complies with IEC61947 standard

### **Advanced energy-saving features**

Advanced lamp technology enables robust energy-saving features. For example, greater brightness control in Auto Light Dimming mode saves considerable energy when the projector is left on without being used. During projection, Auto Lamp Mode automatically adjusts light output to suit the projected scene. When you need to mute the picture temporarily, light output can be completely deactivated to minimise energy consumption.

### **High image quality 3LCD BrightEra™ natural and vivid colour images**

Widescreen WXGA (1280 x 800) 16:10 screen resolution, 3LCD BrightEra™ natural and vivid colour images, plus various Picture Modes for optimising image quality, make the projector one of the best in its class. Thanks to the optical system projecting three basic colours constantly, the projector offers excellent light efficiency, ensuring colourful and bright images. Sony's BrightEra™ panels deliver improved panel light resistance, higher resolution, high brightness and increased panel reliability. High colour reproducibility is important especially when using colourful content, such as materials used in classrooms.

### **Various picture modes for optimal picture quality**

The projector has six available picture modes for correct picture quality: Dynamic, Standard, Presentation, Blackboard, Game, and Cinema. With six picture modes and three brightness modes combined, the user can select the most suitable picture/brightness combination according to the picture source

and environment, to create the optimal image.

## **Network presentation (LAN/Wireless LAN)**

When the projector is installed in a LAN, presentations can be projected from any PC and Mac on the network. A tablet or smartphone can be connected at the same time. You can project jpg, pdf and other supported formats. Up to four users can project PC/Mac images simultaneously, while up to eight users can connect to one projector. For PC/Mac, an application, Projector Station for Network Presentation, is provided. For a tablet/smartphone, an application is provided by Pixelworks, downloaded from the web. For details, please visit: <http://PWPresenter.pixelworks.com>

## **Remote control for iOS device**

Projector Remote is a simple remote control application for Sony's projectors. Networked projectors can be controlled by this remote application. Remote Control allows you to operate the projector with simple and easy-to-read buttons.

## **USB display**

The projector allows you to display pictures and audio\* with one USB cable. You do not need to install any driver for this function. It is a convenient way to connect to the projector when you want to connect easily.

\* There is a time lag in video and audio. When not in simple use, it is recommended to use Line-in or HDMI-in.

## **Input Label**

The input label, which appears in the input menu on screen, can be customised. This gives users a clear understanding of which equipment is connected.

## **Built-in speaker**

The projector includes a 16W monaural speaker.

## Specifications

### Display System

Display System	3 LCD system
----------------	--------------

### Display device

Size of effective display area	0.59" (15 mm) x 3 BrightEra LCD Panel, Aspect ratio: 16:10
--------------------------------	--

Number of pixels	3,072,000 (1280x800 x 3) pixels
------------------	---------------------------------

### Projection lens

Focus	Manual
-------	--------

Zoom - Powered/Manual	Manual
-----------------------	--------

Zoom - Ratio	Approx. x 1.6
--------------	---------------

Throw Ratio	1.40:1 to 2.27:1
-------------	------------------

### Light source

Type	Ultra high pressure mercury lamp
------	----------------------------------

Wattage	210 W type
---------	------------

### Recommended lamp replacement time\*1

Lamp mode: High	4000 H
-----------------	--------

Lamp mode: High 10000 H

---

Lamp mode: Standard 6000 H

---

Lamp mode: Low 10000 H

---

## Filter cleaning / replacement cycle (Max.)\*1

Filter cleaning /  
replacement cycle  
(Max.) 7000 H (cleaning)

---

## Screen size

Screen size 30" to 300" (0.76 m to 7.62 m)  
(measured diagonally)

---

## Light output

Lamp mode: High 3200 lm

---

Lamp mode: Standard 2000 lm

---

Lamp mode: Low 1600 lm

---

## Color light output

Lamp mode: High 3200 lm

---

Lamp mode: Standard 2000 lm

---

Lamp mode: Low      1600 lm

---

## Contrast ratio (full white / full black)\*2

Contrast ratio (full white / full black)      2700:1

---

## Speaker

Speaker      16 W x 1 (monaural)

---

## Displayable scanning frequency

Horizontal      14 kHz to 93 kHz

---

Vertical      47 Hz to 93 Hz

---

## Display resolution

Computer signal input      Maximum display resolution: UXGA  
1600 x 1200 dots\*3

---

Video signal input      NTSC, PAL, SECAM, 480/60i,  
576/50i, 480/60p, 576/50p, 720/60p,  
720/50p, 1080/60i, 1080/50i, The  
following items are available for  
digital signal (HDMI input) only;  
1080/60p, 1080/50p

---

## Color system

Color system	NTSC3.58, PAL, SECAM, NTSC4.43, PAL-M, PAL-N
--------------	--

---

## Keystone correction (Max.)

Vertical	+/-20 degrees
----------	---------------

---

## OSD language

OSD language	24-languages (English, Dutch, French, Italian, German, Spanish, Portuguese, Turkish, Polish, Russian, Swedish, Norwegian, Japanese, Simplified Chinese, Traditional Chinese, Korean, Thai, Vietnamese, Arabic, Farsi, Finnish, Indonesian, Hungarian, Greek)
--------------	--

---

## INPUT OUTPUT (Computer/Video/Control)

INPUT A	RGB / Y PB PR input connector: Mini D-sub 15-pin (female) Audio input connector: Stereo mini jack
---------	---

---

INPUT B	RGB input connector: Mini D-sub 15-pin (female)
---------	---

---

	Audio input connector: Stereo mini jack
INPUT C	HDMI input connector: HDMI 19-pin, HDCP support
S VIDEO IN	S video input connector: Mini DIN 4-pin Audio input connector: Pin jack (x2) (shared with VIDEO IN)
VIDEO IN	Video input connector: Pin jack Audio input connector: Pin jack (x2) (shared with S VIDEO IN)
OUTPUT	Monitor output connector*4: Mini D-sub 15-pin (female) Audio output connector*5: Stereo mini jack (variable out)
REMOTE	RS-232C connector: D-sub 9-pin (male)
LAN	RJ-45, 10BASE-T/100BASE-TX
USB	Type-A
USB	Type-B
MICROPHONE IN	Microphone jack: Mini Jack

## Acoustic noise



---

Lamp mode: Low	30 dB
----------------	-------

---

## Operating temperature / Operating humidity

Operating temperature / Operating humidity	0°C to 40°C (32°F to 104°F) / 35% to 85% (no condensation)
---	--

---

## Storage temperature / Storage humidity

Storage temperature / Storage humidity	-20 °C to +60°C (-4°F to +140°F) / 10% to 90% (no condensation)
---	--

---

## Power requirements

Power requirements	AC 100 V to 240 V, 3.2 A to 1.4 A, 50 Hz / 60 Hz
--------------------	--

---

## Power consumption

AC 100 V to 120 V	Lamp mode: High: 314 W
-------------------	------------------------

---

AC 220 V to 240 V	Lamp mode: High: 301 W
-------------------	------------------------

---

Lamp mode: Low	219 W
----------------	-------

---

## Power Consumption (Standby Mode)

AC 100 V to 120 V	0.5 W (when "Standby mode" is set)
-------------------	------------------------------------

---

AC 100 V to 120 V

to “Low”

AC 220 V to 240 V

0.5 W (when “Standby mode” is set to “Low”)

## Power Consumption (Networked Standby Mode)

AC 100 V to 120 V

5.0 W (LAN)  
 5.6 W (optional WLAN module)  
 5.8 W (All Terminals and Networks Connected) (when "Standby Mode" is set to "Standard")

AC 220 V to 240 V

5.3 W (LAN)  
 5.9 W (optional WLAN module)  
 6.0 W (All Terminals and Networks Connected) (when "Standby Mode" is set to "Standard")

## Standby Mode/Network Standby Mode Activated

Standby Mode/Network Standby Mode Activated

After about 10 minutes

## Wireless Network(s) On/Off Switch

Wireless Network(s) On/Off Switch	<ol style="list-style-type: none"> <li>1) Press the MENU button, then select [Connection/Power]</li> <li>2) [WLAN Settings]</li> <li>3) [WLAN Connection]</li> <li>4) Select On or Off</li> </ol>
--------------------------------------	---

## Heat dissipation

AC 100 V to 120 V	1071 BTU/h
AC 220 V to 240 V	1027 BTU/h

## Dimensions (W x H x D)

Dimensions (W x H x D) (without protrusions)	Approx. 365 x 96.2 x 252 mm (14 3/8 X 3 25/32 X 9 29/32 inches)
---	---

## Mass

Mass	Approx. 3.9 kg (8 lb)
------	-----------------------

## Supplied accessories

Remote commander	RM-PJ8
------------------	--------

## Optional Accessories

Optional Lamp	LMP-E212
---------------	----------

Wireless LAN module	IFU-WLM3
---------------------	----------

## Notes

*1	This figure is expected maintenance time, not guaranteed time. The actual value depends on the environment and how the projector is used
----	--

*2	The value is average.
----	-----------------------

*3	Available for VESA Reduced Blanking signal.
----	---

*4	From INPUT A and INPUT B.
----	---------------------------

*5	Works as an audio switcher function. Output from a selected channel; not available in standby.
----	--

Environmental notice for customers in the USA	Lamp in this product contains mercury. Disposal of these materials may be regulated due to environmental considerations. For disposal or recycling information, please contact your local authorities or see <a href="http://www.sony.com/mercury">www.sony.com/mercury</a> for
---	---

additional information.

---

## Gallery

