

XDCA-FS7

Extension Unit for PXW-FS7



Overview

Extension Unit offers multicamera support for PXW-FS7 including Apple ProRes 422 encoding

While the PXW-FS7 XDCAM camera comes with internal XAVC and MPEG-2 recording on XQD media you can attach the optional XDCA-FS7 Extension Unit. The box is attachable via a MultiPin connector so there are no hassles about cables. The Extension Unit offers additional I/O connectors like Timecode and Genlock for multi-camera operation or the possibility to use common V-Mount batteries. It also allows RAW data output to record 12-bit RAW footage on the AXS-R5 (in combination with HXR-IFR5), or another third party RAW recorder via the FS RAW Interface. The XDCA-FS7 will encode the video stream into the Apple ProRes 422 codec, which is then recorded on to the internal XQD media.

Apple ProRes 422 recording

A built-in Full HD ProRes encoding function enables ProRes-format recording to an XQD card in the camera.

* Firmware update, early 2015.

Allows 12-bit RAW recording on an external recorder

The XDCA-FS7 is needed for PXW-FS7 to record 12-bit RAW footage on the AXS-R5 (in combination with HXR-IFR5), or another third party RAW recorder. The RAW data will be outputted via the FS RAW Interface on the extension unit and is fully compatible with the NEX-FS700 RAW data.

Multi-camera operation

Enables Timecode and Genlock for multi-camera operation or the possibility to use common V-Mount batteries.

Features

Attaches seamlessly to PXW-FS7 camera

The Extension Unit XDCA-FS7 can be connected directly to the PXW-FS7 XDCAM camera to enable the use of functions that support the operator's shooting style or workflow. The unit is attachable via a MultiPin connector so there are no hassles about cables. When using larger lenses, the Extension Unit will balance any possible front heaviness and increase the stability on the shoulder as well.

Apple ProRes 422 recording on XQD card

A built-in Full HD ProRes encoding function enables ProRes-format recording to an XQD card in the camera.

* Firmware update, early 2015.

Allows 12-bit RAW recording on an external recorder

The XDCA-FS7 needed for PXW-FS7 to record 12-bit RAW footage on the AXS-R5 (in combination with HXR-IFR5), or another third party RAW recorder.

Additional I/O connectors for multi-camera operation, plus power support for additional accessories

Timecode and Genlock for multi-camera operation. The unit also provides power connection for additional accessories and or the possibility to use common V-Mount batteries..

Gallery



© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.