


## FWD-55A95L

55" Sony BRAVIA OLED 4K HDR  
Display with Google TV,  
including 3 years PrimeSupport



### Features

#### **World wide colours**

Our brightest and widest shades and hues, all beautifully displayed on a QD-OLED screen powered by Cognitive Processor XR™

#### **Contrast. Unsurpassed.**

Pure blacks bring out extraordinary detail and depth. With Cognitive Processor XR™, the expressive power of QD-OLED is maximised.

#### **Pure blacks. Absolute brightness. Supreme contrast.**

Our brightest ever OLED. With a temperature sensor, high luminance panel and heat diffusion sheet for dissipating heat, this TV detects screen temperature and precisely controls light to deliver 200% as much brightness as its predecessor.

#### **Beautiful colours. Any angle.**

Watching TV from the sides is truly satisfying. Our QD-OLED panel on the A95L keeps luminance constant for consistent colours across all viewing angles.

#### **Everything upscaled close to 4K quality.**

Whatever the content or source, images are upscaled close to 4K. XR 4K Upscaling accesses a vast database to intelligently recreate lost texture and detail.<sup>1</sup>

## **Less noise. Less blur. More clarity in every picture.**

XR Clear Image reduces noise utilising zone division and dynamic frame analysis, and minimises blur.

## **Intelligent motion processing for smooth, fast-moving action.**

XR OLED Motion combats blur by detecting and cross analysing key visual elements on successive frames. It creates and inserts extra frames between the originals for smoother, clearer action.

## **Sound from the screen, truly immersive.**

With Acoustic Surface Audio +™, sound comes directly from the right place in the scene. The screen vibrates, turning every part of it into a speaker for powerful acoustics that perfectly match the picture. Far more immersive than conventional TVs where sound comes from beneath the screen.

## **All your entertainment upscaled to 3D surround sound.**

XR Surround virtually creates surround sound using just the TV speakers for 3D audio without in-ceiling or up-firing speakers. Our BRAVIA XR™ TVs are also compatible with Dolby Atmos®.

## **What you want to watch all in one place.**

Browse 700,000+ movies and TV episodes from across your streaming services, all in one place and organised into topics and genres based on what interests you.<sup>2</sup>

## **Just say what you want to see - Hands-free Voice Search.**

Find favourites faster with voice search. Jump right to a show or movie just by saying it or try browsing with a voice search like “find action movies”. Just say “Ok Google” to get started.

## **Auto HDR Tone Mapping texture and detail.<sup>1</sup>**

Auto HDR Tone Mapping instantly optimises HDR settings during your PS5™ initial setup. Even in dark shadow and bright

highlights, you'll see fine details and true colours.

### **Auto Genre Picture Mode.**

BRAVIA™ automatically switches into Game Mode with PS5™ to minimise lag and maximise responsiveness. It switches back to Standard Mode when watching movies for more expressive scenes.<sup>3</sup>

### **Game Menu - One place for all your game settings.**

Never has it been easier to fine-tune your game status, settings and assist functions. All the essentials are at your fingertips for ease and comfort.<sup>4</sup>

### **Seamless Edge. Almost no bezel.**

Designed virtually frameless, this TV focuses your eyes on what's important - the picture.

### **All your eco in one place.**

The Eco Dashboard keeps all eco-related settings in one place, making it easy to change them individually or in one go.

### **Greater peace of Mind.**

There's the added reassurance of our 3 Years PrimeSupport Professional service package as standard, with access to an elite EU-wide helpdesk for technical support & advanced product exchange handled by local partner, on premise where possible. You can also choose to extend your support for an additional 2 years.

## Specifications

### TV System

TV System (Analog)	B/G,D/K
--------------------	---------

Tuner Channel	45.25MHz-863.25MHz(Depend on
---------------	------------------------------

Coverage (Analog)	country selection)
TV System (Digital Terrestrial)	DVB-T/T2
Tuner Channel Coverage (Digital Terrestrial)	VHF/UHF(Depend on country selection)
TV System (Digital Cable)	DVB-C
Tuner Channel Coverage (Digital Cable)	VHF/UHF/cable(Depend on country selection)
TV System (Digital Sat)	DVB-S/S2
Tuner Channel Coverage (Digital Sat)	Intermediate Frequency 950-2150MHz
Number of Tuners (Terrestrial/Cable)	2(Digital)/1(Analog)
Number of Tuners (Sat)	2
Color System	PAL/SECAM
CI+	Yes
Color Space	sRGB/BT709,BT2020,AdobeRGB,DCI

Operating System	Android 12
------------------	------------

On-board Storage (GB)	32GB
-----------------------	------

## Display Features

X-Anti Reflection	-
-------------------	---

Display type	OLED(QD-OLED)
--------------	---------------

X-Wide Angle	-
--------------	---

Pixel Contrast Booster	Yes
------------------------	-----

Rich Color Enhancer	-
---------------------	---

Backlight dimming type	-
------------------------	---

## Display Specs

Screen Size (inch, measured diagonally)	55"(54.6")
---	------------

Screen Size for WEB(diagonal, cm, integer or 1st decimal)	139cm
---	-------

Backlight type	-
----------------	---

Display resolution (H x	
-------------------------	--

V, pixels)	3840 x 2160
Viewing Angle (Right/Left)	178(89/89) degree
Viewing Angle (Up/Down)	178(89/89) degree
Display Resolution	QFHD
Aspect Ratio	16:9

## Video Features

XR Backlight Master Drive	-
Object-based Super Resolution	XR Super Resolution
Peak Luminance	XR OLED Contrast Pro
TRILUMINOS	XR Triluminos Max
HDR Remaster	XR HDR remaster
Smoothing	XR Smoothing
Features for PlayStation®5 Auto HDR Tone Mapping	Yes
Features for	

PlayStation®5 Auto Genre Picture Mode	Yes
XR Clear Image	Yes
Precision Color Mapping	- (Integrated into XR Triluminos Max)
LED Motion Mode	-
Face Area Detection	Yes
Mastered in 4K	-
Picture modes	Vivid, Standard, Calm, Cinema, IMAX Enhanced, Photo, Professional, Dolby Vision (Vivid/Bright/Dark), FPS Game, RTS Game, Netflix calibrated, BRAVIA CORE calibrated
Auto Wide	Yes
Wide Mode	Full/Vertical Fit/Horizontal Fit/Original Full/Vertical Fit/Horizontal Fit/Original
4:3 Default	-
Video Processing	XR 4K Upscaling
Motion enhancer	XR OLED Motion, Auto mode

Blinking Type	Frame Blinking
24p True Cinema	Yes
Live Colour™ Technology	Yes
PhotoTV HD / BRAVIA 照片秀 for China	Yes
CineMotion/Film Mode/Cinema Drive	Yes
4K Processor	Cognitive Processor XR
HDR (High Dynamic Range) compatibility	Yes(HDR10,HLG,Dolby Vision)
Panel Refresh Rate (Native Hertz)	100/120Hz
Dual database processing	Yes
Dynamic Contrast Enhancer	Yes
<b>Audio Specs</b>	
Channel	2.2ch
Audio Power Output	20W + 20W + 10W + 10W



Speaker Position	Front
Bass/Treble/Balance	Balance
Speaker Type	Acoustic Surface Audio+
Speaker Configuration	Actuator x 2, Subwoofer x 2
DSEE/DSEE-HX	-
Digital audio out (Optical) format	Two channel linear PCM: 48kHz 16bits, Dolby Audio, DTS

## Audio Features

Acoustic Center Sync	Yes (CENTER SPEAKER IN, S-CENTER SPEAKER IN)
Ready for 360 Spatial Sound Personalizer	Yes (via Bluetooth)
Simultaneous Sound Output with TV Speaker	Bluetooth A2DP Device
Vertical Surround Engine	Vertical Surround Engine
Acoustic Auto Calibration	Room & User Position Compensation
Speaker Type-2	-

Clear Phase	Yes
Clear Audio+	-
S-Master	S-Master Digital Amplifier
Auto Surround	Yes
DTS audio format support	DTS Digital Surround, DTS Express, DTS-HD Master Audio, DTS-HD High Resolution Audio, DTS:X
Sound modes	-
Simulated surround sound	S-Force Front Surround
Dolby audio format support	Dolby Audio, Dolby Atmos
Voice Zoom	Voice Zoom 2
HDMI Audio Return Channel(ARC)	Yes (eARC/ARC)
Advanced Auto Volume	Yes
Auto Mute (on no signal)	Yes
FM Radio	-
Audio Out	-

Headphone/Speaker Link	-
HDMI input Audio format	7.1 channel linear PCM: 32/44.1/48/88.2/96/176.4/192kHz 16/20/24bits, Dolby Audio, Dolby Atmos, DTS, DTS Express, DTS-HD Master Audio, DTS-HD High Resolution Audio, DTS:X
ARC output format	Two channel linear PCM: 48kHz 16bits, Dolby Audio, Dolby Atmos, DTS

## Network Features

Control Menu	Yes
ECO Dashboard	Yes
USB Tethering	-
Apple AirPlay	Yes
Apple HomeKit	Yes
Home Network Feature	Home Network Client, Home Network Renderer
Wi-Fi Direct	-
Wi-Fi Certified	Yes

Screen mirroring(Miracast™)	-
Video & TV SideView (iOS/Android)	-
Related Info	-
Wi-Fi Standard	a/b/g/n/ac/ax
Wi-Fi Frequency	2.4GHz/5GHz
Photo Sharing Plus / Photo Share	-
Internet Browser	Yes
Codec for Home Network	MPEG1:MPEG1 / MPEG2PS:MPEG2 / MPEG2TS (HDV,AVCHD):MPEG2,AVC / MP4 (XAVCS):AVC,MPEG4,HEVC / AVI:Xvid,MotionJpeg / ASF (WMV):VC1 / MOV:AVC,MPEG4,MotionJpeg / MKV:Xvid,AVC,MPEG4,VP8.HEVC / WEBM:VP8 / 3GPP:MPEG4,AVC / MP3 / ASF (WMA) / LPCM / WAV / MP4AAC / FLAC,JPEG / HEIF / WEBM:VP9 / AC4 / ogg / AAC / ARW (Screen nail only)
Wireless LAN	Integrated

## Convenience Features

Function by Camera	-
UVC/UAC support	Yes
Multi-View	Yes <sup>*1</sup>
Color Inversion	Yes
TalkBack	Yes
Variable Refresh Rate (VRR)	Yes (for HDMI3/4)
Auto Low Latency Mode (ALLM)	Yes (for HDMI3/4)
Features specified in HDMI2.1	4K120/eARC/VRR/ALLM
Built-in Mic switch	Yes(Left)
X-Protection PRO	Y (with Lightning, Surge, Humidity Protection)
Electronic Program Guide (EPG)	Yes
USB HDD Recording	Yes(1Rec)(Except Italy) <sup>*1</sup>
Twin Picture	Yes

Photo Frame Mode	-
USB playback codecs	MPEG1:MPEG1 / MPEG2PS:MPEG2 / MPEG2TS (HDV,AVCHD):MPEG2,AVC / MP4 (XAVCS):AVC,MPEG4,HEVC / AVI:Xvid,MotionJpeg / ASF (WMV):VC1 / MOV:AVC,MPEG4,MotionJpeg / MKV:Xvid,AVC,MPEG4,VP8.HEVC / WEBM:VP8 / 3GPP:MPEG4,AVC / MP3 / ASF (WMA) / LPCM / WAV / MP4AAC / FLAC,JPEG <sup>*1</sup> / HEIF <sup>*1</sup> / WEBM:VP9 / AC4 / ogg / AAC / ARW (Screen nail only)
Built-in Mic	Yes
Screen Reader	Yes
Audio Description	Yes
Text Magnification	Yes
Accessibility Shortcut	Yes
Switch Access	Yes
Auto Picture Mode	Yes
	ARA / BUL / CAT / HRV / CES / DAN / DUT / ENG / EST / FIN / FRA /

Text Input Language	GER / GRK / HEB / IND / ITA / JPN / NOR / FAS / POL / POR / RON / RUS / SLK / SLV / SPA
Chromecast built-in	Yes
Voice Search	Yes* <sup>2</sup>
Application Store	Yes (Google Play Store)
BRAVIA Sync (including HDMI-CEC)	Yes
Control for HDMI (HDMI CEC)	-
Scene Select	-
i-Manual	Yes
Parental Control	Yes
Channel Block (with password)	Digital
Show/Hide Channels	-
On Screen Clock	Yes
Sleep Timer	Yes
On/Off Timer	Yes
USB drive format	Yes (Supported File System:

support	FAT16/FAT32/exFAT/NTFS)
---------	-------------------------

Display Language	AFR, AMH, ARA, ASM, AZE, BEL, BUL, BEN, BOS, CAT, CZE, DAN, DEU, GRE, ENG, SPA, EST, BAQ, PER, FIN, FRA, GLG, GUJ, HIN, HRV, HUN, IND, ISL, ITA, HEB, JPN, KAZ, KAN, KOR, KIR, LAO, LIT, LAV, MAC, MAL, MON, MAR, MAY, BUR, NOB, NEP, NLD, ORI, PAN, POL, POR, RUM, RUS, SOL, SLV, ALB, SRP, SWE, SWA, TAM, TEL, THA, TGL, TUR, UKR, URD, UZB, VIE ,zh_CN, zh_HK, zh_TW, ZUL
------------------	--

Auto Shut-off	-
---------------	---

## Sensing Features

Sensor	Light/Color
--------	-------------

## General Features

Smart TV	Google TV
----------	-----------

Auto Calibration with CalMAN	Yes
------------------------------	-----

Netflix Calibrated	
--------------------	--



mode	Yes
Tencent Calibrated mode	-
IMAX Certified Model	Yes
Closed Captions (Analog)	-
BRAVIA CORE	10 credits/ 24 months
Closed Captions (Digital)	Subtitle
Demo Mode	-
Emergency Warning System	-
Hotel Mode Menu	-

## Broadcast Features

Teletext	Yes
Teletext number of pages	1000 pages

## Customizing Capability

RS-232C Control -

## Design Features

Style -

Stand Position 2way position (Standard position/Soundbar position)

Stand Color Dark Silver

Bezel Design Seamless edge

Cable Management Yes

Frame color Black

Stand Design Aluminum Edge Stand

Illumination LED -

Stand Swivel -

Stand Tilt -

## Inputs and Outputs

Media Connect -

HDMI Signal 4096x2160p(24,50,60Hz),  
3840x2160p(24,25,30,50,60,100,120Hz)<sup>\*3</sup>,  
1080p(24,30,50,60,100,120Hz),

	1080i(50,60Hz), 720p(24,30,50,60Hz), 576p, 480p
HDCP	HDCP2.3(for HDMI1/2/3/4)
Bluetooth profile support	Version 5.2,HID/HOGP/SPP/A2DP/AVRCP
4K 60P High-Quality formats	HDMI IN1, IN2 ports for 4K(up to 18Gbps) signal, HDMI IN3, IN4 port for 4K(up to 48Gbps) signal
AC Power Input	Pigtail (REAR)
RF (Terrestrial/Cable) Connection Input(s)	1(Side)
IF (Satellite) Input(s)	2(Side)
Composite Video Input(s)	-
Component Video (Y/Pb/Pr) Input(s)	-
HDMI inputs total	4(4Side)
PC In (D-Sub) + Audio In (Stereo Mini)	-

Analog Audio Input(s) (Total)	-
Digital Audio Output(s)	1(Side / Hybrid with S-Center Speaker Input)
Audio Output(s)	-
Headphone Output(s)	-
Subwoofer Output(s)	-
USB ports	2(Side)
Ethernet inputs	1(Side)
RS-232C Input(s)	-
PCMCIA Slot(s)	1(Side)
HDMI PC Input Format	640x480(31.5kHz,60Hz), 800x600(37.9kHz,60Hz), 1024x768(48.4kHz,60Hz), 1280x1024(64.0kHz,60Hz), 1152x864(67.5kHz,75Hz), 1600x900(55.9kHz,60Hz), 1680x1050(65.3kHz,60Hz), 1920x1080(67.5kHz,60Hz), 3840x2160p(30Hz), 3840x2160p(60Hz, 8bits)

## Eco and Energy Saving

Power Requirements (voltage)	220 V - 240 V AC
------------------------------	------------------

Power Requirements (frequency)	50 Hz
--------------------------------	-------

Power Consumption (Home Mode) for WEB	-
---------------------------------------	---

Power Consumption (in Standby)	0.50 W
--------------------------------	--------

Power consumption(Networked Standby)	2.00W(Wi-Fi) / 2.00W(LAN) / 0.50W(CEC)
--------------------------------------	--

SORPLAS	Yes
---------	-----

EEA SDR RANK	F
--------------	---

ECO Friendly	Yes
--------------	-----

On mode power consumption (lot5)	77 kWh/1000h
----------------------------------	--------------

ErP Rank For EU	-
-----------------	---

Peak luminance ratio for EU	-
-----------------------------	---

Mercury content(mg)	0.0
Lead Content	Yes
Dynamic Backlight Control	-
Power Saving Mode / Back Light Off Mode	Yes

## Regulation and Standard Compliance

VESA® Hole Spacing Compatible	Yes
VESA® Hole Pitch(W x H)	30.0 x 30.0 cm

## Measurements (Approx.)

Dimension of TV without Stand with Camera (W x H x D)	Approx. 122.4 x 72.3 x 4.5 (4.28) cm
TV with Stand (Front position) (W x H x D) *Measured incl. camera if bundled	-
TV with Stand (Back position) (W x H x D)	

*Measured incl. camera if bundled	-
Stand Width (Front position style)	-
Stand Width (Back position style)	-
Dimension of TV without Stand (W x H x D)	Approx. 122.4 x 70.7 x 3.4 (2.19) cm
TV with Stand (Standard position) (W x H x D)	Approx. 122.4 x 73.7 x 27.5 cm
TV with Stand (Narrow position) (W x H x D)	-
TV with Stand (Soundbar position) (W x H x D)	Approx. 122.4 x 79.8 x 27.5 cm
Dimension of TV with Floor Stand (W x H x D)	-
Dimension of Package Carton (W x H x D)	Approx. 136.3 x 83.7 x 17.5 cm
Stand width (Standard position)	Approx. 122.3 cm

Stand width (Narrow position)	-
Stand width (Soundbar position)	Approx. 122.3 cm
Floor Stand Width	-
AC Power Adapter size(W x H x D)	-
DC Cable length of AC adaptor(mm)	-
AC Cable Length	1500mm

## Weights (Approx.)

TV with Stand (Front position style/Back position style)	-
Weight of TV without Stand	Approx. 17.6 kg
TV with Stand (Standard position)	Approx. 19 kg
TV with Stand (Narrow position)	-
TV with Stand	



(Soundbar position)	Approx. 19 kg
---------------------	---------------

---

Weight of TV with Floor Stand	-
-------------------------------	---

---

Weight of Package Carton(Gross)	Approx. 24 kg
---------------------------------	---------------

## Carton Spec

Max Qty of carton stacking (vertical)	6
---------------------------------------	---

---

Max Qty of carton stacking (horizontal)	N/A
---	-----

\*only for Shop Front

## Supplied Accessories

Camera Unit (Bundle)	CMU-BC1M
----------------------	----------

---

Voice Remote Control (Supply)	RMF-TX910U
-------------------------------	------------

---

Remote Control	RMT-TX450E
----------------	------------

---

AC Plug Convertor	-
-------------------	---

---

Wall-Mount Bracket	-
--------------------	---

Android TV Setup Guide	-
Batteries	LR03+R03
Floor Stand (Supply)	-
AC Power Adaptor	-
AC Power Cord Spec	(Pig-tail43mm) (EUROPE) (2pin) (round pins Type C)
IR Blaster	-
Support Belt	-
Operating Instructions	EN, FR, ES, NL, DE, PT, IT, SE, DK, FI, NO, PL, CZ, SK, HU, RO, BG, GR, TR
Quick Setup Guide / Supplement CUE (GA)	EN, FR, ES, NL, DE, PT, IT, DK, NO, SE, FI, PL, CZ, SK, HU, RO, BG, GR, TR, RU, UA, AR
Table Top Stand	Separate (Assembly required)

## Optional Accessories

Camera Unit (option)	-
Floor Stand (Option)	-
	SU-WL450(Terminal access limitation, refer to SU-WL450)

Wallmount Bracket product page), SU-WL850(Refer to Country/Area Handling Chart)

## PrimeSupport

Included PrimeSupport 3 Years with advanced exchange handled by local partner, on premise where possible. Optional +2 years extension.

## Notes

\*1 Firmware update may be required.

\*2 Hands Free feature(Built-in Mic) availability depends on language and may need software update. Please check Sony support page for further information; <https://www.sony.net/tv-hf-ww/>

\*3 100Hz and 120Hz is supported by HDMI IN 3 and IN 4

Related products



## **BVM- HX310**

31.1-inch 4K  
TRIMASTER HX™  
Professional Master  
Monitor

## **BVM- HX3110**

30.5-inch 4K  
TRIMASTER HX™  
Professional Master  
Monitor

## Gallery

