

# HDVF-EL75

7.4-inch OLED Viewfinder for portable cameras



## Overview

### **Stunning OLED image quality**

The 7.4-inch\* HDVF-EL75 Viewfinder delivers strikingly high contrast, a wide dynamic range, and a fast response time thanks to the use of revolutionary Organic Light Emitting Diode (OLED) display technology.

OLED panels help prevent light emission when reproducing dark shades, resulting in very deep blacks and a contrast ratio of more than 1,000,000:1. The lack of a backlight allows the device to control all phases of light emission from zero to peak brightness. The innovative technology delivers exceptional colour expression and detail without wasting power, so it is also an exceptional energy-saver.

High Definition acquisition requires extremely precise focusing, so OLED image quality delivers significant benefits by allowing the operator to accurately see contrast and colour levels when framing a shot. A wide viewing angle aids operator comfort while an extremely fast response time is particularly useful for applications such as sports coverage.

In addition, the HDVF-EL75 is packed with a wide range of sophisticated, user-friendly features such as Focus Assist, four assignable switches and a position-adjustment mechanism with unprecedented flexibility.

## Features

7.4-inch, quarter HD (960 x 540) panel with advanced Organic Light Emitting Diode (OLED) display technology.

Quick response for tracking and focusing on moving objects

High contrast and wide dynamic range, thanks to OLED panel characteristics such as deep black colour reproduction and high-peak brightness

Incorporating a 10-bit panel driver, the OLED panel creates smoother-than-ever gradation from dark to bright portions

Stable and long-term colour reproduction with Sony's unique feedback circuit

Focus Assist function supports accurate focusing

Image Magnification function magnifies just the portion of the image that is in the viewfinder display

Peaking Plus function enhances the edge of an object by colour, area selected, or both

Four assignable switches

Waveform Monitor function

Flexible position adjustment mechanism makes it easy to place the viewfinder to suit the operator - or even fold downwards when not in use

Specifications

General	
Power requirements	10.5 V to 17.0 V DC (supplied by the camera)
Power consumption	19.5 W
Operating temperature	-20°C to +45°C (-4°F to +113°F)
Mass	3.5 kg (7 lb 11 oz)
Display Unit	
Panel	7.4-inch (188 mm) colour OLED panel
Effective picture size (H/V, 16:9 aspect ratio)	164 × 92 mm (6 1/2 × 3 5/8 inches)
Effective pixels	960 (H) × 540 (V) × 3 (RGB)
Performance	
Brightness (peak brightness, typical)	350 cd/m <sup>2</sup>
Resolution	500 or more lines
Colour temperature	D65
Supported Formats	
1080	23.98PsF, 24PsF, 25PsF, 29.97PsF, 30PsF, 50i, 59.94i, 60i
720	50p, 59.74p, 60p
Connectors	
Camera connector	Round 20-pin (x1)
Supplied Accessories	
	Indoor hood
	Number plate
	V-wedge shoe attachment
	Hexagonal wrench

---

4 socket head cap screws

---

Cleaning cloth

---

Connecting cable

---

Operation manual

---

Related products



**HDCU-5500**

IP-ready Camera Control Unit (CCU) for HDC-5500 4K/HD system camera



**HDC-5500**

High performance three 2/3-inch 4K CMOS sensor portable system camera with direct 4K output



**HDCU-3100**

IP enabled next generation Camera Control Unit



**HXC-FB80**

Three 2/3-inch Exmor™ CMOS sensor HD colour studio camera



**HDC-3100**

Three 2/3-inch CMOS sensors portable system camera for fibre operation



**HDCU-3170**

IP capable Triax Camera Control Unit



**HDC-3500**

Three 2/3-inch 4K CMOS sensors portable system camera for fibre operation



**HDC-3170**

Three 2/3-inch CMOS sensors portable system camera for triax operation



**HDCU-3500**

IP-ready Camera Control Unit (CCU) for HDC-3500 4K/HD system camera

## Gallery



