

## MDR-M1

New reference closed monitor headphones for creators with ultra-wideband playback.



### Specifications

| General                 |   |
|-------------------------|---|
| Type                    | Closed dynamic  |
| Driver Unit             | 40 mm (1.58 in)   |
| Power Handling Capacity | 1,500 mW (IEC *1)   |
| Impedance               | 50 $\Omega$ at 1kHz   |
| Sensitivity             | 102 dB/mW   |
| Frequency Response      | 5 Hz - 80,000 Hz (JEITA)  |
| Mass                    | Approx. 216 g (without cable)   |
| Included Items          | Headphones cable (approx. 1.2m/2.5 m, Stereo mini plug); Plug adaptor (Stereo standard plug - Stereo mini plug); Warranty card; Reference Guide |

## Notes

\*1

IEC International Electrotechnical  
Commission

---

## Related products



### **MDR-MV1**

Open back Studio  
Monitor Headphones  
for creating spatial  
and stereo sound  
with wide frequency  
range and soundstage  
feel



### **MDR-7506**

Stereo professional  
headphones

## Gallery

