

## Optical Disc Archive Cartridge Generation

### 1

300GB\* , 600GB, 1.2TB and 1.5TB  
disc (Rewritable or Write once)

<br><br>ODC300R, ODC300RE,  
ODC600R, ODC600RE,  
ODC1200RE, ODC1500R



### Overview

#### **Reliable and robust large-capacity media for Optical Disc Archive**

The 1.5 TB capacity write-once optical disc cartridge offers an alternative to LTO or traditional forms of data tape for the longer-term archiving of valuable assets. Sony optical disc cartridges are available in 300 GB\* , 600 GB, 1.2 TB and 1.5 TB capacity sizes, in re-writable and write-once formats.

*\*Product availability may vary by region. ODC300R and ODC300RE are discontinued in North America.*

#### **Low total cost of ownership**

The Sony optical disc cartridges are designed and manufactured to extremely high specifications, offering very fast random access to all content and files. The innovative drive design provides for a 'dual channel' capability and, being file format independent, it can store your assets in a data file format. The system is ideal for a wide range of deep archive requirements as well as near-online news and sports clips requiring fast and random access to any files on the disc. Optical disc complements and co-exists in an established data tape archive strategy.

## **Ideal for deep archive and near-online archive**

The Sony Optical Disc Archive system is ideal for deep archive for very long term archiving, such as broadcaster archives where data tape does not provide the assurance or meet the need for write-once, very long-term archive requirements. It provides second copy archive at a remote site and is ideal for business continuity/disaster recovery, post house and production back-up and for video, film and stock footage archives or national archives. The system can also be used for news and sports clips that need to be near-online and as an on-line browse and proxy clip store.

## Features

### **Optical disc cartridges mounted as a single large volume making file access very simple**

The Sony optical disc cartridge system is designed and manufactured to extremely high specifications, offering a reliable, robust and portable media system for the very long term. Optical disc cartridges are available in 300 GB\*, 600 GB, 1.2 TB and 1.5 TB capacity sizes, in re-writable and write-once formats.

*\*Product availability may vary by region. ODC300R and ODC300RE are discontinued in North America.*

### **Reliable and robust storage with a very long archive life**

Optical disc media is robust and reliable, with a very long shelf life, offering a guaranteed 50+ years archive life. The optical disc cartridge is resilient to temperature extremes, humidity, dust and water.

### **Backwards read compatibility with future generations**

There are no backward compatibility issues and no second-generation media migration is necessary, as the optical disc

cartridge will maintain backwards read compatibility with future optical disc drives.

### **File format independent**

Files are written as data and any kind of data format can be archived for increased flexibility. The system is UDF compatible.

### **Reduces total cost of ownership and environmental storage cost**

Optical disc cartridges total cost of ownership over their extended archive life will significantly reduce because of their minimal environmental storage demands.

### **Offline media management by Cartridge Memory (CM)**

Basic metadata can be stored on the Cartridge Memory to make it easier to locate data files.

### **Fast access to data files**

Using an IT file data structure means data files can be accessed directly and randomly for flexibility and faster search capabilities. This function offers significant speed benefits over LTO tape for accessing short clips and allows the Optical Disc Archive system to work as near-line archive for production systems, as well as deep archive for the long term.

## Specifications

### Specifications

Disc

Archival Disc

Total capacity

ODC1500R: 1500 GB (1.5TB)  
 ODC1200RE: 1200 GB (1.2TB)  
 ODC600R: 600GB  
 ODC600RE: 600GB

|                      |   |
|----------------------|---|
|                      | ODC300R*: 300GB<br>ODC300RE*: 300GB   |
| Recording type       | ODC1500R: Write Once<br>ODC1200RE: Rewritable<br>ODC600R: Write Once<br>ODC600RE: Rewritable<br>ODC300R*: Write Once<br>ODC300RE*: Rewritable |
| Read cycle           | ODC1200RE: 1,000 cycles<br>ODC600RE: 1,000 cycles<br>ODC300RE*: 1,000 cycles  |
| Operating conditions | 5 ~ 55 deg.   |
| Storage conditions   | -10 ~ 55 deg. / 3 ~ 90%RH (Short term)<br>10 ~ 30 deg. / 30 ~ 70%RH (Long term *recommended)  |
| Archival life        | 50 year(estimated)  |
|                      | <i>*Product availability may vary by region. ODC300R and ODC300RE are discontinued in North America.</i>                                      |

Related products



## ODS-D55U

Optical Disc Archive standalone drive unit with transfer speeds 330 Mbps (read) and 210 Mbps (write-once disc) or 130 Mbps (rewritable disc)



## ODS-D77UA

ODS-D77UA has very high transfer speeds. Read is 1.1Gbps. Write-once is 440 Mbps and Rewritable is 160 Mbps (verify on). Performance varies based on type of cartridge.



## ODS-L30M

\*Please contact your local sales representative for details.



## ODS-L100E

\*Please contact your local sales representative for details.

## ODS-L60E

\*Please contact your local sales representative for details.

## File Server mode License for FM2

\*Please contact your local sales representative for details.

## ODS-D380U

\*Please contact your local sales representative for details.

## Gallery

